





## Technical data

### 1204S

Double-row self-aligning ball bearings

Self-aligning ball bearing, pressed steel cage, open

#### VISUAL (S)



# 1204S

## Double-row self-aligning ball bearings

### PRODUCT DEFINITION

<b>Brand</b>	NTN
<b>d - Internal diameter</b>	20 mm
<b>D - External diameter</b>	47 mm
<b>B - Bearing/Inner ring width</b>	14 mm
<b>rs - Min fillet radius</b>	1 mm
<b>Radial clearance class</b>	CN
<b>Precision class</b>	P0
<b>Mass</b>	0,12 kg

### PRODUCT PERFORMANCE

<b>C - Dynamic load</b>	10000000 mN
<b>C0 - Static load</b>	2610000 mN
<b>Cu - Fatigue limit load</b>	110000 mN
<b>e - Coefficient</b>	0.29
<b>Y0 - Static axial load coefficient</b>	2.3
<b>Y1 - Lower axial load coefficient</b>	2.2
<b>Y2 - Upper axial load coefficient</b>	3.4
<b>N lim - Oil lubrication limit speed</b>	102000 %/s
<b>N lim - Grease lubrication limit speed</b>	84000 %/s
<b>Tmin - Min operating temperature</b>	253,15 °K
<b>Tmax - Max operating temperature</b>	393,15 °K

### ABUTMENT

<b>da min - Min shoulder diameter IR</b>	25 mm
<b>Da max - Max shoulder diameter OR</b>	42 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

# 1204S

Double-row self-aligning ball bearings

## ABUTMENT

**ra max - Max shaft & housing fillet radius**

1 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15