

Nylon toggle DuoTec

Easy to install nylon toggle for high loads in all panel building materials



Kitchen hanging cabinets



Shelves

7

Applications

- Kitchen hanging cabinets
- Living room cabinets
- Shelves
- Wardrobes
- Handrails
- Pictures
- Mirrors
- Lamps
- Heavy hanging baskets

Advantages

- Flexible screw mount allows for the use of screws and hooks with different thread shapes.
- Glass fibre-reinforced plastics and a metal skeleton insert (fischer DuoTec 12) allow the toggle to handle heavy tensile and transverse loads in all panel building materials.
- Soft grey nylon contact surface distributes the load over the panel surface, thereby minimising weakening of the supporting building material.
- Standard drill hole diameters and short tilting element for easy installation in narrow cavities, including cavities with insulation.
- White flush sleeve with snap function allows the plug to be pre-installed quickly and securely in the drill hole.
- With scale on the grip strap (fischer DuoTec 12) for determining the required screw length (scale value + 20 mm).

Certificates



Building materials

Suitable for:

- Gypsum plasterboard
- Gypsum fibreboard
- Wooden panels, such as OSB boards, chipboard, MDF sheets
- Steel plates
- Plastic boards
- Hollow blocks made from concrete


Also functioning in:

- Solid materials, such as concrete and wood


Functioning

- The fischer DuoTec is designed for pre-positioned installation.
- Simple installation with a standard diameter 10 or 12 mm drill bit.
- The short toggle element makes it suitable for narrow and even with mineral wool insulated cavities. Note the length of the toggle element!
- Functions like an expansion plug in solid building materials such as concrete or wood. Note, not with metric screws!
- Flexible screw insert allows for the use of wood, chipboard and metric screws and hooks.


Installation in board materials



Installation in cavities



7



Technical data in board material

Nylon toggle fischer DuoTec



Item	Item No.	Drill hole diameter d_0 [mm]	Min. panel thickness d_p [mm]	Max. panel thickness d_p [mm]	Min. cavity depth a [mm]	Screw diameter d_s [mm]	Screw length l_s [mm]	Sales unit [pcs]
fischer DuoTec 10 S	537259 ¹⁾	10	12	55	40	5,0	60	25
fischer DuoTec 10	537258	10	12	55	40	—	$\geq d_p + t_{fix} + 20$	50
fischer DuoTec 10 S PH	539025 ²⁾	10	12	55	40	—	60	25
fischer DuoTec 12	542796	12	12	55	50	—	$\geq d_p + t_{fix} + 20$	10
fischer DuoTec 12 RH	542798 ⁴⁾	12	12	55	50	5,5	70	10
fischer DuoTec 12 S PH M	542797 ³⁾	12	12	55	50	—	70	10



1) fischer DuoTec S - with chipboard screw countersunk head

2) fischer DuoTec S PH - with chipboard screw panhead

3) fischer DuoTec S PH M - with machine screw panhead

4) fischer DuoTec RH - with screw with round hook

Installation for hits in solid building materials



7

Technical data in solid materials

Nylon toggle fischer DuoTec



		Drill hole diam- eter d_0 [mm]	Min. drill hole depth h_1 [mm]	Screw diameter [mm]	Min. screw length l_s [mm]	Anchor length l [mm]	Max. fixture thickness t_{fix} [mm]	Sales unit [pcs]
Item	Item No.							
fischer DuoTec 10 S	537259 ¹⁾	10	65	5,0	60	50	27	25
fischer DuoTec 10	537258	10	$l_s - t_{fix} + 10$	4,5 - 5,0	$t_{fix} + 55$	50	$l_s - 55$	50
fischer DuoTec 10 S PH	539025 ²⁾	10	65	5,0	60	50	27	25
fischer DuoTec 12	542796	12	$l_s - t_{fix} + 10$	5,0 - 6,0	$t_{fix} + 65$	60	$l_s - 65$	10
fischer DuoTec 12 RH	542798 ³⁾	12	75	5,5	55	60	—	10

1) fischer DuoTec S - with chipboard screw countersunk head
2) fischer DuoTec S PH - with chipboard screw panhead
3) fischer DuoTec RH - with screw with round hook

Loads

Nylon toggle DuoTec									
Recommended loads ^{1) 2)} for a single anchor.									
Type		DuoTec 10				DuoTec 12			
		Chipboard screws		Metrical screw	fischer Hook	Chipboard screws		Metrical screw	fischer Hook
Screw diameter	[mm]	4.5	5.0	5.0	5.0	5.0	6.0	6.0	5.5
Recommended loads in the respective base material $F_{rec}^{3)}$ for a span in the construction $b = 625 \text{ mm}$									
Gypsum plasterboard	9.5 mm	[kN]	0.17	0.17	0.17	0.17	0.17	0.17	0.17
Gypsum plasterboard	12.5 mm	[kN]	0.20	0.20	0.20	0.20	0.20	0.20	0.20
Gypsum plasterboard	2 x 12.5 mm	[kN]	0.43	0.43	0.43	0.30 ⁴⁾	0.43	0.43	0.43
Gypsum fibreboard	12.5 mm	[kN]	0.51	0.51	0.51	0.30 ⁴⁾	0.51	0.51	0.50 ⁴⁾
Chipboard	16 mm	[kN]	0.71	0.71	0.71	0.30 ⁴⁾	0.75	0.80	0.50 ⁴⁾
OSB board	18 mm	[kN]	0.75	0.75	0.75	0.30 ⁴⁾	0.75	1.30	0.50 ⁴⁾
Recommended loads in the respective base material $F_{rec}^{3)}$ for a span in the construction $b = 120 \text{ mm}$									
Gypsum plasterboard	9.5 mm	[kN]	0.20	0.20	0.20	0.20	0.20	0.20	0.20
Gypsum plasterboard	12.5 mm	[kN]	0.36	0.36	0.36	0.30 ⁴⁾	0.36	0.36	0.20
Gypsum plasterboard	2 x 12.5 mm	[kN]	0.59	0.59	0.59	0.30 ⁴⁾	0.70	0.80	0.50 ⁴⁾
Gypsum fibreboard	12.5 mm	[kN]	0.75	0.75	0.75	0.30 ⁴⁾	0.80	1.10	0.50 ⁴⁾
Chipboard	16 mm	[kN]	0.75	0.75	0.75	0.30 ⁴⁾	0.80	1.40	0.50 ⁴⁾
OSB board	18 mm	[kN]	0.75	0.75	0.75	0.30 ⁴⁾	0.80	1.50	0.50 ⁴⁾
Recommended loads in solid building materials $F_{rec}^{3)}$									
Concrete	$\geq C20/25$	[kN]	0.45	0.75	-	0.30 ⁴⁾	0.40	0.75	0.30
Wood		[kN]	0.30	0.75	-	0.30 ⁴⁾	0.20	0.65	0.30
Recommended loads in the respective base material $F_{rec}^{3)}$									
Hollow block of lightweight aggregate concrete 'Sapa Parpaing'	$f_b \geq 8 \text{ N/mm}^2$	[kN]	-	-	-	-	0.65	1.00	0.50 ⁴⁾
Pre-stressed hollow-core concrete slabs		[kN]	-	-	-	-	1.00	1.40	0.50 ⁴⁾
Lightweight concrete hollow block Hbl acc. to EN 771-3	$f_b \geq 2 \text{ N/mm}^2$	[kN]	-	-	-	-	0.90	1.00	0.50 ⁴⁾

¹⁾ Required safety factors are considered.

²⁾ The recommended loads are reference values and depending to the building material and the workmanship. The values are only valid for the given screw diameter.

³⁾ Valid for tensile load, shear load and oblique load under any angle.

⁴⁾ Bending of the hook is decisive. Only for tension load.