


Geberit Mapress Carbon Steel T-piece, reduced (FKM, blue)



Example image



APPLICATION PURPOSES

- For district heating water ≤ 140 °C
- For thermal media (solar)
- For mineral and lubricating oil
- For motor fuels (e.g. diesel)
- For compressed air (oil purity class 3–4)

- For solar technology, industry and shipbuilding

- Pressing socket with black protection plug

CHARACTERISTICS

- Pressing indicator
- Outside zinc-plated
- Seal ring made of FKM, blue

TECHNICAL DATA

Product material	Non-alloy steel 1.0034 E195 (EN 10305)
------------------	--

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
51356	15 / 12 / 15	18	15	18	90	6.8	4.2	3.4	3.4	1.4	2.2	1.4
51357	20 / 12 / 20	22	15	22	90	7.4	4.4	3.7	3.7	1.6	2.4	1.6
51359	20 / 15 / 20	22	18	22	90	7.4	4.4	3.7	3.7	1.6	2.4	1.6
51362	25 / 12 / 25	28	15	28	90	8.4	4.7	4.2	4.2	1.9	2.7	1.9
51364	25 / 15 / 25	28	18	28	90	8.4	4.7	4.2	4.2	1.9	2.7	1.9

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
51366	25 / 20 / 25	28	22	28	90	8.4	4.8	4.2	4.2	1.9	2.7	1.9
51367	32 / 12 / 32	35	15	35	90	10	5.1	5	5	2.4	3.1	2.4
51368	32 / 15 / 32	35	18	35	90	10	5.1	5	5	2.4	3.1	2.4
51369	32 / 20 / 32	35	22	35	90	10	5.2	5	5	2.4	3.1	2.4
51370	32 / 25 / 32	35	28	35	90	10	5.5	5	5	2.4	3.2	2.4
51373	40 / 20 / 40	42	22	42	90	11.4	5.5	5.7	5.7	2.7	3.4	2.7
51374	40 / 25 / 40	42	28	42	90	11.4	5.8	5.7	5.7	2.7	3.5	2.7
51375	40 / 32 / 40	42	35	42	90	11.4	6.1	5.7	5.7	2.7	3.5	2.7
51378	50 / 20 / 50	54	22	54	90	13.8	6.1	6.9	6.9	3.4	4	3.4
51379	50 / 25 / 50	54	28	54	90	13.8	6.4	6.9	6.9	3.4	4.1	3.4
51380	50 / 32 / 50	54	35	54	90	13.8	6.8	6.9	6.9	3.4	4.2	3.4
51381	50 / 40 / 50	54	42	54	90	13.8	7.2	6.9	6.9	3.4	4.2	3.4
51390	65 / 25 / 65	76.1	28	76.1	90	23	7.5	11.5	11.5	6.2	5.2	6.2

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
51391	65 / 32 / 65	76.1	35	76.1	90	23	7.9	11.5	11.5	6.2	5.3	6.2
51392	65 / 40 / 65	76.1	42	76.1	90	23	8.3	11.5	11.5	6.2	5.3	6.2
51393	65 / 50 / 65	76.1	54	76.1	90	23	8.9	11.5	11.5	6.2	5.4	6.2
51396	80 / 25 / 80	88.9	28	88.9	90	26	8.1	13	13	7	5.8	7
51397	80 / 32 / 80	88.9	35	88.9	90	26	8.5	13	13	7	5.9	7
51398	80 / 40 / 80	88.9	42	88.9	90	26	8.9	13	13	7	5.9	7
51399	80 / 50 / 80	88.9	54	88.9	90	26	9.5	13	13	7	6	7
51405	100 / 50 / 100	108	54	108	90	31	10.5	15.5	15.5	8	7	8
51407	100 / 65 / 100	108	76.1	108	90	31	12.6	15.5	15.5	8	7.3	8
51408	100 / 80 / 100	108	88.9	108	90	31	13.7	15.5	15.5	8	7.7	8