# Product data sheet Characteristics

# XCLJ567H29

LIMIT SWITCH XCLJ - red body steel - roller plunger- NC and NC slow contacts



#### Main

OsiSense XC	
Standard format	
Limit switch	
XCLJ	
Form C conforming to CENELEC EN 50041	
Fixed	
Plunger head	
	Standard format  Limit switch  XCLJ  Form C conforming to CENELEC EN 50041  Fixed

#### Complementary

Complementary	
Material	Metal
Body material	Zamak
Head material	Zamak
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Spring return roller plunger metal
Switch actuation	By 30° cam
Type of approach	Lateral approach, 1 or 2 programmable direction
Electrical connection	Screw-clamp terminals, clamping capacity: 1 x 0.52 x 2.5 mm²
Cable entry	1 entry tapped for M20 x 1.5 cable gland, cable outer diameter: 713 mm
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contacts insulation form	Zb
Contact operation	Slow-break, break before make
Number of steps	1
Positive opening	With
Positive opening minimum force	28 N
Minimum force for tripping	14 N
Maximum actuation speed	1 M/S
[le] rated operational current	3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	500 V (pollution degree 3) conforming to IEC 60947-1
Maximum resistance across terminals	25 MOhm conforming to IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	IEC 60664 6 kV IEC 60947-1 6 kV
Short-circuit protection	10 A cartridge fuse, type gG

Electrical durability	5000000 Cycles, DC-13, inductive load type, 120 V, 4 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 Cycles, DC-13, inductive load type, 24 V, 10 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 Cycles, DC-13, inductive load type, 48 V, 7 W, operating rate <60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
Mechanical durability	25000000 Cycles
Width	40 Mm
Height	77 Mm
Depth	44 Mm
Net weight	0.455 Kg
Terminals description ISO n°1	(13-14)NO (21-22)NC

### Environment

Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27	
Vibration resistance	25 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK07 conforming to EN 50102	
Overvoltage category	Class I conforming to IEC 61140	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4070 °C	
Standards	CENELEC EN 50041 EN/IEC 60947-5-1 EN 60204-1	

## Packing Units

i acking critis	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	446 G
Package 1 Height	4.3 Cm
Package 1 width	7 Cm
Package 1 Length	13 Cm
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Weight	4.658 Kg
Package 2 Height	15 Cm
Package 2 width	15 Cm
Package 2 Length	40 Cm

## Offer Sustainability

REACh Regulation	REACh Declaration	
EU RoHS Directive	Not applicable, out of EU RoHS legal scope	
Environmental Disclosure	Product Environmental Profile	

## Contractual warranty

Warranty	18 months

Product Life Status : Commercialised

