

UFS3-37N517

UFS

FORK SENSORS





Ordering information

Туре	Part no.
UFS3-37N517	6075478

Illustration may differ

Other models and accessories → www.sick.com/UFS



Detailed technical data

Features

Functional principle	Ultrasonic detection principle
Dimensions (W x H x D)	20 mm x 37.4 mm x 70 mm
Housing design	Fork shaped
Fork width	2.6 mm
Fork depth	42.5 mm
Minimum detectable object (MDO)	Label size: 2 mm ¹⁾ Label gap: 1 mm ¹⁾
Label detection	✓
Adjustment	Teach-in button, cable (Teach-in, sensitivity, light/dark switching, Teach-in dynamic)
Teach-in mode	1-point teach-in 2-point teach-in Teach-in dynamic

 $^{^{1)}}$ Depends on the label thickness.

Mechanics/electronics

Supply voltage	10 V DC 30 V DC ¹⁾
Ripple	< 10 % ²⁾
Current consumption	50 mA ³⁾
Switching frequency	1.1 kHz ⁴⁾
Response time	440 μs ⁵⁾

 $^{^{1)}}$ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ May not fall below or exceed U_{V} tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.

⁶⁾ Output current minimal 0.03 mA.

 $^{^{7)}}$ Reference voltage DC 50 V.

Jitter	40 μs
Switching output	NPN
Switching output (voltage)	NPN: HIGH = V_S / LOW \leq 3 V
Switching mode	Light/dark switching
Output current I _{max.}	100 mA ⁶⁾
Input, teach-in (ET)	Teach: U < 2 V: Run: U = 10 V < U _V
Initialization time	100 ms
Connection type	Cable with M12 male connector, 4-pin, 0.31 m
Cable diameter	Ø 3.5 mm
Protection class	III ⁷⁾
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP65
Weight	Approx. 100 g
Housing material	Zamak Glass fiber reinforced plastic
Indication	LED indicator green: power on LED indicator, yellow: Status switching output Q

 $^{^{1)}}$ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

Communication interface

IO-Link	√ , V1.1
Data transmission rate	COM3 (230,4 kBaud)
Cycle time	4 ms
VendorID	26
DeviceID HEX	0x8002A6
DeviceID DEC	8389286
Process data length	16 Bit
Process data structure A	Bit 0 = switching signal Q_{L1} Bit 1 = switching signal Q_{L2} Bit 2 = switching signal Q_{Int1} Bit 3 = switching signal Q_{Int2} Bit 4 = alarm Q_{OR} Bit 5 = Teach busy Bit 6 15 = measured value
Digital output	Q_1
Number	1

²⁾ May not fall below or exceed U_V tolerances.

³⁾ Without load.

⁴⁾ With light/dark ratio 1:1.

⁵⁾ Signal transit time with resistive load.

⁶⁾ Output current minimal 0.03 mA.

 $^{^{7)}}$ Reference voltage DC 50 V.

Ambient data

Ambient operating temperature	+5 °C +55 °C ¹⁾
Ambient temperature, storage	-20 °C +70 °C
Shock load	According to EN 60068-2-27
EMC	EN 60947-5-2 ²⁾
UL File No.	NRKH.E191603 & NRKH7.E191603

 $^{^{1)}}$ Do not bend below 0 $^{\circ}\text{C}.$

Connection type/pinouts

Connection type	Cable with M12 male connector, 4-pin, 0.31 m
Connection type Detail	
Cable diameter	Ø 3.5 mm
Conductor cross section	0.14 mm ²
Cable material	PVC
Length of cable	0.265 m
Length of male connector	4.5 cm
Pinouts	
BN 1	+ (L+)
WH 2	MF
BU 3	- (M)
BK 4	Q/C

Smart Task

Smart Task name Base logics


Classifications


ECLASS 5.0	27270909
ECLASS 5.1.4	27270909
ECLASS 6.0	27270909
ECLASS 6.2	27270909
ECLASS 7.0	27270909
ECLASS 8.0	27270909
ECLASS 8.1	27270909
ECLASS 9.0	27270909
ECLASS 10.0	27270909
ECLASS 11.0	27270909
ECLASS 12.0	27270909
ETIM 5.0	EC002720
ETIM 6.0	EC002720
ETIM 7.0	EC002720
ETIM 8.0	EC002720
UNSPSC 16.0901	39121528


²⁾ The sensor complies with the Radio Safety Requirements (EMC) for the industrial sector (Radio Safety Class A). It may cause radio interference if used in a residential area

Dimensional drawing (Dimensions in mm (inch))

Dimensional drawing, sensor







- ① Fork depth
- ② Fork width③ Fixing hole
- Detection axis
- ⑤ Connection (see technical data for length of cable)
- ⑤ Display and adjustment elements

Dimensional drawing, connection type




Cable with M12 male connector

① Connection (see technical data for length of cable)

Pinouts


Pinouts, see table Technical data: Connection type/pinouts



M12 male connector, 4-pin, A-coding

Adjustments

Display and adjustment elements



- ① LEDs (status display)
- ② Teach-in button
- 3 Bar graph

Recommended accessories

Other models and accessories → www.sick.com/UFS

	Brief description	Туре	Part no.
Connection modules			
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A	IOLA2US-01101 (SiLink2 Master)	1061790
Universal bar	clamp systems		
	WFS mounting rod, straight, including 2 x fixing screws, Aluminum	BEF-M12GF-A	2059414
00	Bar clamp for bar diameter of 12 mm (fixing the mounting rod), Aluminum, 2 screws M6 x 30, 2 spring discs	BEF-RMC-D12	5321878
	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235
Sensor Integra	ation Gateway		
	 Further functions: Web server integrated, IIoT interface available (dual talk) Logic editor: no Communication interface: IO-Link, Ethernet, PROFINET, REST API, MQTT, OPC UA Product category: IO-Link Master 	SIG350-0004AP100	6076871
	Further functions: Web server integrated, IIoT interface available (dual talk) Logic editor: no Communication interface: IO-Link, Ethernet, EtherNet/IP™, REST API, MQTT, OPC UA Product category: IO-Link Master	SIG350-0005AP100	6076923
	 Further functions: Web server integrated, IIoT interface available (dual talk) Logic editor: no Communication interface: IO-Link, Ethernet, EtherCAT®, REST API, MQTT, OPC UA Product category: IO-Link Master 	SIG350-0006AP100	6076924

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

