

## Han E-Male Contact-c Au 5,5 mm<sup>2</sup> / 10 AWG




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 33 000 6139  |
| Specification      | Han E-Male Contact-c Au 5,5 mm <sup>2</sup> / 10 AWG                          |
| HARTING eCatalogue | <a href="https://harting.com/09330006139">https://harting.com/09330006139</a> |

### Identification

|                 |                    |
|-----------------|--------------------|
| Category        | Contacts           |
| Series          | Han E <sup>®</sup> |
| Type of contact | Crimp contact      |

### Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Gender                | Male              |
| Manufacturing process | Turned contacts   |

### Technical characteristics

|                               |                     |
|-------------------------------|---------------------|
| Conductor cross-section       | 5.5 mm <sup>2</sup> |
| Conductor cross-section [AWG] | AWG 10              |
| Rated current                 | ≤16 A               |
| Contact resistance            | ≤1 mΩ               |

### Material properties

|                             |  |
|-----------------------------|--|
| Material (contacts)         | Copper alloy   |
| Surface (contacts)          | Gold plated  |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50   |
| REACH Annex XVII substances | Not contained  |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
|----------------|--------------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 100  |
| Net weight                     | 1.527 g                                    |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140049840                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |