

# Vigi iC60 - earth leakage add-on block - 2P - 25A - 100mA - AC type

Local distributor code: 396791793

396791793 A9V12225

EAN Code: 3606480087479

#### Main

Range	Acti9	
Product name	Acti9 Vigi iC60	
Product or component type	Add-on residual current device	
Device short name	Vigi iC60	
Poles description	2P	
[In] rated current	25 A	
Earth-leakage sensitivity	100 mA	
Earth-leakage protection time delay	Instantaneous	
Earth leakage protection type	Type AC	
Network type	AC	
Network frequency	50/60 Hz	
[Ue] rated operational voltage	230415 V AC 50/60 Hz conforming to EN/IEC 61009-1 230415 V AC 50/60 Hz conforming to EN/IEC 61009-2-1	
Standards	EN/IEC 61009-1 EN/IEC 61009-2-1	
9 mm pitches	3	

## Complementary

Device location in system	Outgoer	
Residual current tripping technology	Voltage independent	
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2	
Range compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 Reflex iC60	
Product compatibility	Single terminal	
Local signalling	Trip indicator	
Mounting mode	Clip-on	
Mounting support	DIN rail	
Electrical connection to mcb	By screws	
Comb busbar and distribution block compatibility	Bottom: YES	
Height	91 mm	
Width	63 mm	

Depth	73.5 mm	
Net weight	0.165 kg	
Connections - terminals	Tunnel type terminal downside for 1 cable(s) 125 mm² rigid without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible with cable end	
Wire stripping length	14 mm for bottom connection	
Tightening torque	2 N.m bottom	

### **Environment**

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529	
Pollution degree	3 conforming to IEC 60947-2	
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to IEC 61009-1	
Ambient air temperature for operation	-560 °C	
Ambient air temperature for storage	-4085 °C	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	7.8 cm
Package 1 Length	11.5 cm
Package 1 Weight	135 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.141 kg

## **Logistical informations**

Country of origin FR

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

<b>⊘</b> Environmental footprint	
Total lifecycle Carbon footprint	3
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	E30d8de5-e712-4620-931e-4a4cf9525d5a
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins