


1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Optional remote signaling module for 4-pos. surge arresters and base elements from the VALVETRAB SPP product family.



Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466701
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL138Z
Product key	CL138Z
GTIN	4063151861131
Weight per piece (including packing)	24.4 g
Weight per piece (excluding packing)	18.3 g
Customs tariff number	85363030
Country of origin	DE

SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Technical data

Product properties

Product type	Remote signaling set
Product family	VAL-SPP
Type	Installation module
Number of positions	4

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
-------------------------	---------------

Indicator/remote signaling


Connection name	Remote fault indicator contact
Switching function	Changeover contact
Max. required back-up fuse	1 A (gG)
AC operating voltage	5 V AC ... 250 V AC (≤ 2000 m (amsl) at pollution degree 2) 5 V AC ... 150 V AC ($\leq \text{Ⓢ} \downarrow \downarrow \downarrow$ m (amsl))
AC operating current	5 mA AC ... 1 A AC
DC operating voltage	30 V DC ($\leq \text{Ⓢ} \downarrow \downarrow \downarrow$ m (amsl))
DC operating current	1 A DC
DC operating voltage	125 V DC ($\leq \text{Ⓢ} \downarrow \downarrow \downarrow$ m (amsl))
DC operating current	200 mA DC
Insulation type	The product has double/reinforced insulation between the main and auxiliary circuit.

Connection data

Remote fault indicator contact

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section flexible	0.25 mm ² ... 1.5 mm ²
Conductor cross section rigid	0.25 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ² (Stripping length 8 mm)
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 0.75 mm ² (Stripping length 8 mm)

Dimensions

Dimensional drawing	
---------------------	--

SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Width	71.2 mm
Height	16.9 mm
Depth	34.9 mm
Horizontal pitch	4 Div.

Material specifications

Color	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PBT
Material group	I
Housing material	PBT

Protective circuit

Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous voltage U_C	250 V AC
Short-circuit current rating I_{SCCR}	100 A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (operating voltage remote contact ≤ 150 V) ≤ 2000 m (operating voltage remote contact ≤ 250 V)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Approvals

UL indicator/remote signaling

Operating voltage	250 V AC
DC operating voltage	30 V DC
AC operating current	5 mA AC ... 1 A AC
DC operating current	1 A DC

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018
Standards/specifications	EN 60947-5-1
Note	2018

SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Mounting

Mounting type	on base element
---------------	-----------------


SPP-R-4 - Remote signaling module

1466701


<https://www.phoenixcontact.com/gb/products/1466701>

Drawings

Dimensional drawing




Dimensional drawing



The figure shows the product when plugged in with VAL-SPP-T2-275-3+1-UT-R surge arrester

Circuit diagram



SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1466701>



IECEE CB Scheme

Approval ID: NL-109184

CCA

Approval ID: NTR NL-8052



KEMA-KEUR

Approval ID: 71-138153 REV.2



cULus Recognized

Approval ID: E330181

SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Classifications

ECLASS

ECLASS-13.0	27171292
-------------	----------

ETIM

ETIM 9.0	EC002496
----------	----------

SPP-R-4 - Remote signaling module



1466701

<https://www.phoenixcontact.com/gb/products/1466701>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk