



54V XR FLEXVOLT 52mm SDS–Max Hammer Drill (52 mm) (2 X 12 Ah)

DCH775X2–QW

True corded performance

An anti rotation system detects a loss of tool control, and reacts by instantly cutting the power

Active vibration control system incorporating a floating rear handle and damped side handle to reduce vibration

Rotation–stop for demolition applications in brick, masonry and light chasing in concrete

Wireless Tool Control transmitter which allows the tool to be wirelessly paired with another Wireless Tool Control device, such as a dust extractor, for automatic activation and shut down



Battery Chemistry

Li–Ion

Battery Capacity

9 Ah

Power Source

Cordless

No Load Speed

145–290 Rpm

Impact energy (EPTA 05/2009)

19.399999999999999 J

Max. Drilling Capacity (Concrete)

52 mm