

1806037

https://www.phoenixcontact.com/gb/products/1806037

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 6 mm², Connection method: Crimp, Contact connection type: Pin, cable length: 350

## Commercial data

Item number	1806037
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ABLBAA
Product key	ABLBAA
GTIN	4046356688949
Weight per piece (including packing)	33.63 g
Weight per piece (excluding packing)	33.197 g
Customs tariff number	85444290
Country of origin	DE



1806037

https://www.phoenixcontact.com/gb/products/1806037

#### Technical data

#### Notes

#### Safety note

Safety note

- WARNING: Commission properly functioning products only.
   The products must be regularly inspected for damage.
   Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at phoenixcontact.com/products under the product
- The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
- Use a protective cap to protect connectors that are not in use.
   The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.



1806037

https://www.phoenixcontact.com/gb/products/1806037

Material Housing

Material Contact carrier

	<ul> <li>Observe the minimum bending radius of the cable. Lay the cable without twisting it.</li> </ul>
roduct properties	
Product type	Panel feed-through
Product family	SUNCLIX
Number of positions	1
Insulation characteristics	
Protection class	II
Degree of pollution	2
onnection data	
Conductor connection	
Tightening torque	1.8 Nm ±0.1 Nm
imensions	
Dimensional drawing	18,6 41,6
Width	26.3 mm
Height	26.3 mm
Length	41.5 mm
ectrical properties	
Rated voltage (III/2)	1000 V
Rated surge voltage (III/2)	12 kV
Rated current (6.0 mm²)	40 A
Contact resistance	0.45 mΩ
Contact resistance	≤ 0.45 mΩ (when plugged in (without cable))
echanical properties	
Mechanical data	
Insertion/withdrawal cycles	100
Insertion force	45 N ±10 N
Withdrawal force	250 N ±50 N (when locked)
laterial specifications	
Color	black
Color of the housing part	black

PPE

PPE



1806037

https://www.phoenixcontact.com/gb/products/1806037

Material Contact	Cu
Material Seal	EPDM
Material Contact surface	Ag
Flammability rating according to UL 94	V0
Insulating material group	III
Insulating material	mPPE
Contact surface	Silver Ag
Cable seal material	Elastosil LR 3065/50
Outer sheath, material	PE-X

## Cable/line

Cable length	350 mm
Cable type	Railway cable
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	84x0.3
Cable type	Railway cable Radox GKW-S
Cable structure	tin-plated, fine-wired, IEC 60228 Class 5
External cable diameter	5.40 mm ±0.15 mm
	5.10 mm 4.95 mm 5.25 mm ±0.15 mm
Outer sheath, material	PE-X
External sheath, color	black
Single wire, material	Cu
Single wire, cross section	6 mm²
Cable cross section	6 mm²
Smallest bending radius, fixed installation	10.2 mm (2x Ø)
Smallest bending radius, movable installation	15.3 mm (3x Ø)
Cable pull-out force	> 80 N
Halogen-free	yes
Resistance to oil	yes
Flame resistance	yes

#### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP66/IP68 (2 m / 24 h)
Degree of protection (not plugged in)	IP20
Degree of protection	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C 85 °C
Ambient temperature (assembly)	-25 °C 50 °C
Resistance to oil	yes

## Standards and regulations

Flame resistance	yes
Resistance to oil	yes



1806037


https://www.phoenixcontact.com/gb/products/1806037

## Drawings

# 18,6

Dimension x = cable length c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm

## Dimensional drawing






1806037

https://www.phoenixcontact.com/gb/products/1806037

## Dimensional drawing



a: anti-rotation protection

b: coding

c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm



1806037

https://www.phoenixcontact.com/gb/products/1806037

## **Approvals**

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1806037



TÜV Rheinland

Approval ID: R 60165003-0001



1806037

https://www.phoenixcontact.com/gb/products/1806037

## Classifications

	A 000

	ECLASS-13.0	27440107	
E <sup>-</sup>	ГІМ		
	ETIM 9.0	EC002635	
UNSPSC			
	UNSPSC 21.0	39121400	



1806037

https://www.phoenixcontact.com/gb/products/1806037

## Environmental product compliance

#### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions	
China RoHS		
Environment friendly use period (EFUP)	EFUP-E	
	No hazardous substances above the limits	
EU REACH SVHC		
REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)	
SCIP	89d11822-de39-44d8-b987-66fc31bf0bc4	

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk