







WIRING DIAGRAMS		LOCKNUT LN-P18		SPECIFICATIONS																																																					
 <p>OUTPUT: AP6X</p> <p>SHORT-CIRCUIT AND OVERLOAD PROTECTED</p>				<table><tr><td>OPERATING VOLTAGE</td><td>10-30 VDC</td></tr><tr><td>RIPPLE</td><td>≤10%</td></tr><tr><td>HYSTERESIS (DIFFERENTIAL TRAVEL)</td><td>3-15% (5% TYPICAL)</td></tr><tr><td>VOLTAGE DROP ACROSS CONDUCTING SENSOR</td><td>≤1.8 V at 200 mA</td></tr><tr><td>OUTPUT FUNCTION</td><td>NORMALLY OPEN 3-WIRE DC SELF-CONTAINED</td></tr><tr><td>TTL COMPATIBLE</td><td>NO</td></tr><tr><td>SHORT-CIRCUIT PROTECTED</td><td>YES</td></tr><tr><td>TRIGGER CURRENT FOR OVERLOAD PROTECTION</td><td>≥220 mA</td></tr><tr><td>CONTINUOUS LOAD CURRENT</td><td>≤200 mA</td></tr><tr><td>LEAKAGE (OFF-STATE) CURRENT</td><td>&lt;10 μA</td></tr><tr><td>NO-LOAD CURRENT</td><td>5.5-9.5 mA</td></tr><tr><td>TIME DELAY BEFORE AVAILABILITY</td><td>≤8 ms</td></tr><tr><td>POWER-ON EFFECT PROTECTION</td><td>INCORPORATED</td></tr><tr><td>POLARITY INVERSION PROTECTION</td><td>INCORPORATED</td></tr><tr><td>WIRE-BREAK PROTECTION</td><td>INCORPORATED</td></tr><tr><td>PROTECTION AGAINST TRANSIENTS</td><td>2 kV, 1 ms, 1 kΩ</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr><tr><td>ENCLOSURE</td><td>MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67</td></tr><tr><td>SHOCK</td><td>30 g, 11 ms</td></tr><tr><td>VIBRATION</td><td>55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)</td></tr><tr><td>LED FUNCTION</td><td>RED: OUTPUT ENERGIZED</td></tr><tr><td>SENSING RANGE</td><td>8 mm = .315" (NOMINAL)</td></tr><tr><td>SWITCHING FREQUENCY</td><td>1000 Hz</td></tr><tr><td>REPEATABILITY</td><td>≤2% of NOMINAL SENSING RANGE</td></tr><tr><td>SHIELDED</td><td>NO</td></tr></table>				OPERATING VOLTAGE	10-30 VDC	RIPPLE	≤10%	HYSTERESIS (DIFFERENTIAL TRAVEL)	3-15% (5% TYPICAL)	VOLTAGE DROP ACROSS CONDUCTING SENSOR	≤1.8 V at 200 mA	OUTPUT FUNCTION	NORMALLY OPEN 3-WIRE DC SELF-CONTAINED	TTL COMPATIBLE	NO	SHORT-CIRCUIT PROTECTED	YES	TRIGGER CURRENT FOR OVERLOAD PROTECTION	≥220 mA	CONTINUOUS LOAD CURRENT	≤200 mA	LEAKAGE (OFF-STATE) CURRENT	<10 μA	NO-LOAD CURRENT	5.5-9.5 mA	TIME DELAY BEFORE AVAILABILITY	≤8 ms	POWER-ON EFFECT PROTECTION	INCORPORATED	POLARITY INVERSION PROTECTION	INCORPORATED	WIRE-BREAK PROTECTION	INCORPORATED	PROTECTION AGAINST TRANSIENTS	2 kV, 1 ms, 1 kΩ	OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67	SHOCK	30 g, 11 ms	VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)	LED FUNCTION	RED: OUTPUT ENERGIZED	SENSING RANGE	8 mm = .315" (NOMINAL)	SWITCHING FREQUENCY	1000 Hz	REPEATABILITY	≤2% of NOMINAL SENSING RANGE	SHIELDED	NO
OPERATING VOLTAGE	10-30 VDC																																																								
RIPPLE	≤10%																																																								
HYSTERESIS (DIFFERENTIAL TRAVEL)	3-15% (5% TYPICAL)																																																								
VOLTAGE DROP ACROSS CONDUCTING SENSOR	≤1.8 V at 200 mA																																																								
OUTPUT FUNCTION	NORMALLY OPEN 3-WIRE DC SELF-CONTAINED																																																								
TTL COMPATIBLE	NO																																																								
SHORT-CIRCUIT PROTECTED	YES																																																								
TRIGGER CURRENT FOR OVERLOAD PROTECTION	≥220 mA																																																								
CONTINUOUS LOAD CURRENT	≤200 mA																																																								
LEAKAGE (OFF-STATE) CURRENT	<10 μA																																																								
NO-LOAD CURRENT	5.5-9.5 mA																																																								
TIME DELAY BEFORE AVAILABILITY	≤8 ms																																																								
POWER-ON EFFECT PROTECTION	INCORPORATED																																																								
POLARITY INVERSION PROTECTION	INCORPORATED																																																								
WIRE-BREAK PROTECTION	INCORPORATED																																																								
PROTECTION AGAINST TRANSIENTS	2 kV, 1 ms, 1 kΩ																																																								
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																								
ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67																																																								
SHOCK	30 g, 11 ms																																																								
VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)																																																								
LED FUNCTION	RED: OUTPUT ENERGIZED																																																								
SENSING RANGE	8 mm = .315" (NOMINAL)																																																								
SWITCHING FREQUENCY	1000 Hz																																																								
REPEATABILITY	≤2% of NOMINAL SENSING RANGE																																																								
SHIELDED	NO																																																								
																																																									
				<table><tr><td colspan="2">MATERIAL PA 12-GF30 PLASTIC BARREL</td><td colspan="2">3RD ANGLE PROJECTION</td><td colspan="2" rowspan="4"><div>TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224</div></td></tr><tr><td colspan="2">FINISH</td><td colspan="6">PART NO.</td></tr><tr><td>DRWN GMB</td><td>DATE 5/9/89</td><td colspan="6" rowspan="2">Ni8-S18-AP6X-H1141</td></tr><tr><td>CHKD</td><td>DATE</td></tr><tr><td colspan="2">TMI</td><td>SIZE B</td><td>ID NO.</td><td colspan="2">4652600</td><td>REV A</td></tr><tr><td colspan="2">DIMENSIONS ARE IN INCHES mm</td><td colspan="2">SCALE NONE</td><td colspan="2">BPQD-D\4652600</td><td>SHEET OF</td></tr></table>				MATERIAL PA 12-GF30 PLASTIC BARREL		3RD ANGLE PROJECTION		 <div>TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224</div>		FINISH		PART NO.						DRWN GMB	DATE 5/9/89	Ni8-S18-AP6X-H1141						CHKD	DATE	TMI		SIZE B	ID NO.	4652600		REV A	DIMENSIONS ARE IN INCHES mm		SCALE NONE		BPQD-D\4652600		SHEET OF												
MATERIAL PA 12-GF30 PLASTIC BARREL		3RD ANGLE PROJECTION		 <div>TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224</div>																																																					
FINISH		PART NO.																																																							
DRWN GMB	DATE 5/9/89	Ni8-S18-AP6X-H1141																																																							
CHKD	DATE																																																								
TMI		SIZE B	ID NO.	4652600		REV A																																																			
DIMENSIONS ARE IN INCHES mm		SCALE NONE		BPQD-D\4652600		SHEET OF																																																			
A	SEE REVISION DOCUMENT CP-NS18	RJP	9/18/92																																																						
REV	DESCRIPTION	DRFT	DATE	CHKD																																																					
REVISIONS																																																									