


## FEATURES

- **Nylon 12 material:** Provides high durability and flexibility
- **9.5 mm inside diameter:** Ensures optimal flow capacity
- **Abrasion resistant:** Extends the lifespan of the tubing in harsh conditions
- **Chemical resistant:** Suitable for use with various chemicals without degradation
- **Moisture resistant:** Prevents damage from exposure to moisture
- **Maximum operating pressure of 14 bar:** Supports high-pressure applications
- **Temperature range from -30 °C to 60 °C:** Suitable for diverse environmental conditions

## RS PRO 9.5 mm Flexible Tubing, Nylon 12

RS Stock No: 631-949



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO flexible tubing is designed for high-performance applications requiring durability and reliability. Made from Nylon 12, it is ideal for use in demanding environments such as air brake systems and food production lines. Its natural colour and robust construction make it suitable for a variety of industrial applications, offering excellent resistance to abrasion, chemicals, and moisture.

### General Specifications

Application	Air Brake, Food Production Line, Fuel, Lubrication, Pneumatic
Colour	Natural
Material	Nylon 12
Maximum Operating Pressure	14 bar
Number of Tubes	1
Product Type	Flexible Tubing
Resistance Features	Abrasion Resistant, Chemical Resistant, Moisture Resistant

### Mechanical Specifications

Inside Diameter	9.5 mm
Length	30 m
Outside Diameter	12 mm

### Operation Environment Specifications

Maximum Operating Temperature	60 °C
Minimum Operating Temperature	-30 °C

### Approvals

Standards/Approvals	BS 5409, DIN 73378, DIN 74324, ISO 7628, RoHS 3
---------------------	---