



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Cable-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Power Positions	2
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	500 VDC
-------------------	---------



Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	3 μm[118.11 μin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Silver
Contact Mating Area Plating Material	Silver (Ag)
Contact Type	Tab
Contact Current Rating (Max)	40 A

Termination Features

Termination Post & Tail Length	2.9 mm[.114 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Hold-Down
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	LCP GF30 (Liquid Crystal Polymer)
Centerline (Pitch)	7.8 mm[.307 in]

Dimensions

Connector Width	10.3 mm[.4 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	12.3 mm[.48 in]
Connector Length	18.9 mm[.74 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application



Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	150
Packaging Method	Tape

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1982299-3
ELCON MINI 2P CABLE CONN,WITH CODING(B)




TE Part # 1982299-1
ELCON MINI 2P CABLE CONN,WITH CODING(R)

Also in the Series | ELCON Mini



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(19)



Rectangular Connector Housings(6)



Rectangular Power Connectors(25)




Standard Rectangular Connectors(6)

Customers Also Bought



TE Part #2057426-3
IMP100S,H,V2P10C,UG,OEW46,5.5



TE Part #2328874-1
QSFP28, 1X4, CAGE ASSEMBLY, SPRING, HS




TE Part #5223985-8
UPM KEYED GUIDE PIN



TE Part #2007788-3
IMP100S,H,V3P10C,UG,OEW39,5.5




TE Part #2132529-3
IMP100S,H,V3P6C,LG,REW39,5.5



TE Part #2187510-1
SW PIR HDR BP, 100OHM, 4X6 OEW



TE Part #6450542-8
MBXL VERT RCPT 7P+40S



TE Part #2187307-1
TinMan Header Assy 4x16 Open



TE Part #2007847-3
[IMP100S,H,V5P10C,RG,LEW39,5.5](#)



TE Part #2007805-3
[IMP100S,H,V3P16C,UG,LEW39,5.5](#)

Documents

Product Drawings

[ELCON MINI 2P VERT HEADER,W/ CODING](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2042274-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2042274-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2042274-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ELCON Mini Power Interconnects QRG \(English\)](#)

English

Product Specifications

[Application Specification](#)

English