

## FEATURES

- **Panel Mount Design:** Easy installation and integration into existing systems.
- **Wide Voltage Range:** Operates between 90 V AC and 550 V AC, accommodating various electrical environments.
- **Temperature Range:** Functions effectively from -20 °C to 70 °C, suitable for diverse conditions.
- **Compact Size:** With dimensions of 144 mm x 144 mm x 55.5 mm, it fits neatly into control panels.
- **Standards Approved:** Complies with CE, cULus, DEKRA, IEC, and more, ensuring reliability and safety.

## RS PRO Panel Mount Power Factor Controller, 550 V AC

RS Stock No: 631-062



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power factor controller is designed to optimise the efficiency of electrical systems by managing and improving power factor. Ideal for industrial applications, it ensures reduced energy consumption and cost savings by maintaining an optimal power factor.

## General Specifications

Mount Type	Panel
Product Type	Power Factor Controller
Sub Type	Power Factor Controller

## Mechanical Specifications

Height	55.5 mm
Length	144 mm
Width	144 mm

## Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-20 °C

## Electrical Specifications

Maximum Supply Voltage	550 V ac
Minimum Supply Voltage	90 V ac

## Approvals

Standards/Approvals	CE, cULus, DEKRA, IEC, I Net, K-Q TSE-ISO-EN 9000, MID
---------------------	--