

## Europe connectors - EC 25 TR - 3240185


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide Europe terminal strip, transparent, for connecting solid conductors and stranded conductors with ferrules with a cross section of 10 to 25 mm<sup>2</sup>

RoHS

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 457897
GTIN	4046356457897
Weight per Piece (excluding packing)	117.440 g
Custom tariff number	85369010
Country of origin	Austria
Note	Made to Order (non-returnable)

### Technical data

#### General

Number of positions	12
Number of levels	1
Number of connections	24
Nominal cross section	25 mm <sup>2</sup>
Color	transparent
Insulating material	PA
Flammability rating according to UL 94	V2
Ambient temperature (operation)	-40 °C ... 110 °C
Maximum load current	101 A (with 25 mm <sup>2</sup> conductor cross section)
Nominal current I <sub>N</sub>	101 A (with 25 mm <sup>2</sup> conductor cross section)
Nominal voltage U <sub>N</sub>	750 V
Open side panel	No

## Europe connectors - EC 25 TR - 3240185

### Technical data

#### Dimensions

Width	30 mm
Length	187.3 mm
Height	28 mm
Depth	30 mm
Drill hole spacing	16 mm
Pitch	16 mm

#### Connection data

Connection method	Screw connection
Conductor cross section solid min.	10 mm <sup>2</sup>
Conductor cross section solid max.	25 mm <sup>2</sup>
Conductor cross section AWG min.	8
Conductor cross section AWG max.	4
Conductor cross section flexible min.	10 mm <sup>2</sup>
Conductor cross section flexible max.	25 mm <sup>2</sup>
Min. AWG conductor cross section, flexible	8
Max. AWG conductor cross section, flexible	4
Conductor cross section flexible, with ferrule without plastic sleeve min.	4 mm <sup>2</sup>
Conductor cross section flexible, with ferrule without plastic sleeve max.	16 mm <sup>2</sup>
Conductor cross section flexible, with ferrule with plastic sleeve min.	4 mm <sup>2</sup>
Conductor cross section flexible, with ferrule with plastic sleeve max.	10 mm <sup>2</sup>
2 conductors with same cross section, solid min.	4 mm <sup>2</sup>
2 conductors with same cross section, solid max.	6 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	2.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	4 mm <sup>2</sup>
Stripping length	9 mm
Screw thread	M5
Tightening torque, min	2 Nm
Tightening torque max	3 Nm

#### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V2

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

# Europe connectors - EC 25 TR - 3240185

## Classifications

### eCl@ss

eCl@ss 4.0	27141106
eCl@ss 4.1	27141106
eCl@ss 5.0	27141106
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141106
eCl@ss 8.0	27141106
eCl@ss 9.0	27141106

### ETIM

ETIM 3.0	EC001284
ETIM 4.0	EC001284
ETIM 5.0	EC001284
ETIM 6.0	EC001284

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121409

## Approvals


### Approvals

#### Approvals

UL Recognized / cUL Recognized / cULus Recognized


#### Ex Approvals

### Approval details


UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
	D	B	C
Nominal voltage UN	600 V	600 V	600 V
Nominal current IN	85 A	85 A	85 A
mm <sup>2</sup> /AWG/kcmil	8-4	8-4	8-4

## Europe connectors - EC 25 TR - 3240185

### Approvals

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
----------------	---	---	--------------

	D	B	C
Nominal voltage UN	600 V	600 V	600 V
Nominal current IN	85 A	85 A	85 A
mm <sup>2</sup> /AWG/kcmil	8-4	8-4	8-4

cULus Recognized	
------------------	---