

## TF-F585

### Torque wrench TORCOFIX FS

without pre-set

Code	ETIM
<b>3288277</b>	<b>EC002132</b>
EAN	UNSPSC
<b>4010886965603</b>	<b>27-11-17-15</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-22</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Controlled screw tightening in the range of 17 - 85 Nm /12 - 63 lbf-ft
- Triggering and robust pipe torque wrench with fixed setting
- Versions with SE 14x18 insert socket
- For controlled right- and left-hand tightening (insert tool for change of direction)
- Proven and robust release mechanism
- Compact Design
- New ergonomic handle
- Tamper-proof Cap at the End of the Handle
- Factory depth gauge: 17.5 mm (9x12 mm)
- Operation only with end fittings with standardised depth gauges, otherwise inaccuracies can arise
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/-3 % deviation and thus with a greater precision than the standard-stipulated +/-4 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- If fixed setting at the factory is desired is required, please state the Nm / lbf-ft value when ordering (price on request)
- OPTIONAL: 2in1 Adjustment and Locking Tool TF-EFS25 (Code: 3254941)

### Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [lbf-ft]	<b>12 lbf-ft - 63 lbf-ft</b>
Net weight [kg]	<b>0,34 kg</b>	Drive connector rectangular	<b>9 x 12 mm</b>
Total length [mm]	<b>329 mm</b>	Backup	<b>Catch lock</b>
Total width [mm]	<b>22 mm</b>	Trigger mechanism	<b>Short path triggering</b>
Total height [mm]	<b>18,5 mm</b>	Precision +/-	<b>+/- 3 %</b>
Depth gauge [metric]	<b>17,5 mm</b>	Direction of tightening	<b>Left and right</b>
Torque (min.) [N·m]	<b>17 Nm</b>	Fixed setting	<b>yes</b>
Torque (max.) [N·m]	<b>85 Nm</b>	Test certificate	<b>DIN EN ISO 6789-2:2017</b>
Torque (min.) [lbf-ft]	<b>12 lbf-ft</b>	Calibration length	<b>276,5 mm</b>
Torque (max.) [lbf-ft]	<b>63 lbf-ft</b>	Storage/Content	<b>Plastic box</b>
Torque range (min./max.) [N·m]	<b>17 Nm - 85 Nm</b>		