

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 200MM

Fixed

KF5BA200-325L



Part Number

Swivel

KP5BA200-325L




Swivel and brake

KP5BD200-325L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	200 mm		
Overall Height H	240 mm ±1		
Size of plate A X B	129 x 106 mm±1		
Plate hole centres a x b	105 x 80 mm±0,3		
Plate hole	11 mm		
Offset F ±1	\	48 mm	48 mm
Width of Tread	45 mm±0,5		
Hardness of tread	shore A ± 88		
Load capacity	200 Kg		
Weight	1,5 kg	2,0 kg	2,5 kg
Temperature	- 10 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
Tread : Thermoplastic rubber, grey non marking.
Hub : Plain bore.

Features :

Low starting effort,
Bonded Rubber,
Corrosion resistant, easy to clean
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Medium duty.