Parker Product Datasheet



This range of ergonomic polymer couplers has been designed for the safety of operators and machinery while giving very high energy efficiency performance.
Available in three profile standards, it is perfectly suited for any type of installation.

PART NUMBER: 9094U08 10
COUPLING HALF: Plug
BODY MATERIAL: Steel
CONNECTION TYPE: Tube
SLEEVE MATERIAL: No sleeve
DIAMETER: ND 8
CONNECTION SIZE: 10MM
PROFILE: ISO B

PRODUCT OVERVIEW

This range of ergonomic polymer couplers has been designed for the safety of operators and machinery while giving very high energy efficiency performance.

Available in three profile standards, it is perfectly suited for any type of installation.

Features/Benefits:

- Safety & Reliability

• Prevents risk of whiplash
• Quick-acting vent allowing disconnection to be carried out in total safety

• Rotating sleeve to avoid risk of accidental disconnection
• Low connection/disconnection force even under pressure
• Polymer sleeve protects equipment from scratching
• Protective spiral over the tube prevents kinking

- Performance

• Very high flow and low pressure drop
• 100% leak-tested in production
• Date coding to guarantee quality and traceability
• Robust impact-resistant material
• Optimum energy efficiency
• Long-term reliability

- Easy-to-Use

• Immediate identification by clear marking on each model showing:
profile of the compatible male probe
type part number
• Compatible with male probes conforming to:
ISO B profile
European profile
ARO profile

Markets:

• Packaging
• Miscellaneous Manufacturing
• Vehicle Assembly Facilities

Applications:

• Compressed Air Circuits Automatic Connection and Disconnection
• Workshops
• Air Operated Tools
• Ring Main Circuits
• Cleaning
• Blowing

Technologies:

• Quick acting coupler
• Quick coupling
• Quick connect coupling
• Quick connect coupler
• Y coupler
• Coupler
• Coupling
• C9000

Technical Characteristics:

• Compatible fluids: Compressed air
• Materials: Technical polymer, aluminium, nickel-plated brass, zamak, stainless steel
• Pressure: Vacuum to 16 bar
• Temperature: -20°C to +60°C

Regulations:

• DI: 97/23/EC (PED)
• DI: 2002/95/EC (RoHS), 2011/65/EC
• DI: 1907/2006 (REACH)
• ISO 4414 Pneumatic Fluid Power: General Rules Relating to Systems
• DIN EN 983 Safety Standard for Pneumatics

Product Types:

• Coupler, Male BSPP Thread
• Coupler, Male BSPT Thread
• Coupler, Female BSPP Thread
• Coupler, LF 3000® Push-In Connection, Body Spiral Protection Spring
• Coupler with Hosetail
• Coupler, Bulkhead Mountable, Female BSPP Thread
• Y Coupler, Female BSPP Thread
• Probe, Straight-Through, Male BSPP Thread
• Probe, Straight-Through, Female BSPP Thread
• Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
• Probe, Straight-Through, with Hosetail
• Coupler, Male BSPP Thread
• Coupler, Female BSPP Thread

- Coupler, LF 3000® Push-In Connection, with Spiral Protection Spring
- Coupler with Hosetail
- Coupler, Bulkhead Mountable, Female BSPP Thread
- Y Coupler, Female BSPP Thread
- Probe, Straight-Through, Male BSPP Thread
- Probe, Straight-Through, Female BSPP Thread
- Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
- Probe, Straight-Through, with Hosetail
- Coupler, Male BSPP Thread
- Coupler, Male BSPT Thread
- Coupler, Female BSPP Thread
- Coupler, LF 3000® Push-In Connection, with Spiral Protection Spring
- Coupler, Bulkhead Mountable, Female BSPP Thread
- Y Coupler, Female BSPP Thread
- Probe, Straight-Through, Male BSPP Thread
- Probe, Straight-Through, Female BSPP Thread
- Probe, Straight-Through, Male BSPT Thread
- Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
- Probe, Straight-Through, with Hosetail

TECH SPECIFICATIONS

DIVISION	Low Pressure Connectors Europe Division
FUNCTION	Straight-Through
CONNECTION SIZE	10 mm
INTERCHANGE TYPE	ISO B Profile
DIVISION	Low Pressure Connectors Europe Division
OPERATION TYPE	No Sleeve
BRAND	Parker
BODY MATERIAL	Steel
SEAL MATERIAL	Without Seal
MAXIMUM OPERATING TEMPERATURE	140 °F
SLEEVE MATERIAL	Without Sleeve

COUPLING HALF	Plug
QUANTITY PER BOX	5
MINIMUM OPERATING TEMPERATURE	-20 °C
DIAMETER	8 mm (nominal)
MINIMUM OPERATING TEMPERATURE	-4 °F
PRODUCT SERIES	Series C9000
PRODUCT TYPE	Quick Coupling
TECHNOLOGY	Pneumatics
INDUSTRY	Industrial Manufacturing Equipment
MAXIMUM OPERATING PRESSURE	233 psi
FLOW RATE	2400 L/min (air)
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
APPLICATION	Workshops, Cleaning, Blowing, Pneumatics, Air-Operated Tools, Ring Main Circuits, Packaging
PLATING TYPE	Nickel-Plated
BRAND	Legris
MAXIMUM OPERATING PRESSURE	16 bar
MAXIMUM OPERATING TEMPERATURE	60 °C
COMPATIBLE FITTING	C9000 Coupler
VALVE INCLUDED	No
CONNECTION TYPE	Hose Barb
WEIGHT	0.028 kg