



PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS)

RS Components

Chemwatch Hazard Alert Code: 1

Chemwatch: 5422-08

Version No: 2.1.1.1

Safety Data Sheet according to WHS and ADG requirements

Issue Date: 26/08/2020

Print Date: 07/09/2020

L.GHS.AUS.EN

SECTION 1 Identification of the substance / mixture and of the company / undertaking

Product Identifier

| | |
|-------------------------------|--|
| Product name | PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS) |
| Synonyms | Not Available |
| Other means of identification | Not Available |

Relevant identified uses of the substance or mixture and uses advised against

| | |
|--------------------------|--|
| Relevant identified uses | Industrial uses, metal working fluids. |
|--------------------------|--|

Details of the supplier of the safety data sheet

| | |
|-------------------------|--|
| Registered company name | RS Components |
| Address | 25 Pavese Street Smithfield NSW 2164 Australia |
| Telephone | +1 300 656 636 |
| Fax | +1 300 656 696 |
| Website | www.au.rs-online.com |
| Email | Not Available |

Emergency telephone number

| | |
|-----------------------------------|------------------------------|
| Association / Organisation | CHEMWATCH EMERGENCY RESPONSE |
| Emergency telephone numbers | +61 2 9186 1132 |
| Other emergency telephone numbers | +61 1800 951 288 |

Once connected and if the message is not in your preferred language then please dial 01

SECTION 2 Hazards identification

Classification of the substance or mixture

NON-HAZARDOUS CHEMICAL. NON-DANGEROUS GOODS. According to the WHS Regulations and the ADG Code.

ChemWatch Hazard Ratings

| | Min | Max |
|--------------|-----|-----|
| Flammability | 1 | 1 |
| Toxicity | 0 | 0 |
| Body Contact | 1 | 1 |
| Reactivity | 0 | 0 |
| Chronic | 0 | 0 |

0 = Minimum
1 = Low
2 = Moderate
3 = High
4 = Extreme

| | |
|--------------------|----------------|
| Poisons Schedule | Not Applicable |
| Classification [1] | Not Applicable |

Label elements

| | |
|---------------------|----------------|
| Hazard pictogram(s) | Not Applicable |
| Signal word | Not Applicable |

Hazard statement(s)

Not Applicable

Precautionary statement(s) Prevention

Not Applicable

Precautionary statement(s) Response

Not Applicable

Precautionary statement(s) Storage

Not Applicable

Precautionary statement(s) Disposal

Not Applicable

SECTION 3 Composition / information on ingredients**Substances**

See section below for composition of Mixtures

Mixtures

| CAS No | %[weight] | Name |
|---------------|-----------|-------------------------|
| Not Available | 100 | ingredient, proprietary |

SECTION 4 First aid measures**Description of first aid measures**

| | |
|---------------------|--|
| Eye Contact | If this product comes in contact with eyes: <ul style="list-style-type: none"> ▶ Wash out immediately with water. ▶ If irritation continues, seek medical attention. ▶ Removal of contact lenses after an eye injury should only be undertaken by skilled personnel. |
| Skin Contact | If skin or hair contact occurs: <ul style="list-style-type: none"> ▶ Flush skin and hair with running water (and soap if available). ▶ Seek medical attention in event of irritation. |
| Inhalation | <ul style="list-style-type: none"> ▶ If fumes, aerosols or combustion products are inhaled remove from contaminated area. ▶ Other measures are usually unnecessary. |
| Ingestion | <ul style="list-style-type: none"> ▶ If swallowed do NOT induce vomiting. ▶ If vomiting occurs, lean patient forward or place on left side (head-down position, if possible) to maintain open airway and prevent aspiration. ▶ Observe the patient carefully. ▶ Never give liquid to a person showing signs of being sleepy or with reduced awareness; i.e. becoming unconscious. ▶ Give water to rinse out mouth, then provide liquid slowly and as much as casualty can comfortably drink. ▶ Seek medical advice. |

Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5 Firefighting measures**Extinguishing media**

- ▶ Water spray or fog.
- ▶ Foam.
- ▶ Dry chemical powder.
- ▶ BCF (where regulations permit).

Special hazards arising from the substrate or mixture

| | |
|-----------------------------|-------------|
| Fire Incompatibility | None known. |
|-----------------------------|-------------|

Advice for firefighters

| | |
|------------------------------|--|
| Fire Fighting | <ul style="list-style-type: none"> ▶ Alert Fire Brigade and tell them location and nature of hazard. ▶ Wear breathing apparatus plus protective gloves. ▶ Prevent, by any means available, spillage from entering drains or water courses. ▶ Use water delivered as a fine spray to control fire and cool adjacent area. |
| Fire/Explosion Hazard | <ul style="list-style-type: none"> ▶ Combustible. ▶ Slight fire hazard when exposed to heat or flame. ▶ Heating may cause expansion or decomposition leading to violent rupture of containers. ▶ On combustion, may emit toxic fumes of carbon monoxide (CO). |
| HAZCHEM | Not Applicable |

SECTION 6 Accidental release measures**Personal precautions, protective equipment and emergency procedures**

See section 8

Environmental precautions

PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS)

See section 12

Methods and material for containment and cleaning up

| | |
|---------------------|---|
| Minor Spills | <ul style="list-style-type: none"> ▶ Clean up all spills immediately. ▶ Avoid contact with skin and eyes. ▶ Wear impervious gloves and safety goggles. ▶ Trowel up/scrape up. |
| Major Spills | <ul style="list-style-type: none"> ▶ Clear area of personnel and move upwind. ▶ Alert Fire Brigade and tell them location and nature of hazard. ▶ Control personal contact with the substance, by using protective equipment. ▶ Prevent spillage from entering drains, sewers or water courses. |

Personal Protective Equipment advice is contained in Section 8 of the SDS.

SECTION 7 Handling and storage**Precautions for safe handling**

| | |
|--------------------------|---|
| Safe handling | <ul style="list-style-type: none"> ▶ Limit all unnecessary personal contact. ▶ Wear protective clothing when risk of exposure occurs. ▶ Use in a well-ventilated area. ▶ Avoid contact with incompatible materials. |
| Other information | <ul style="list-style-type: none"> ▶ Store in original containers. ▶ Keep containers securely sealed. ▶ No smoking, naked lights or ignition sources. ▶ Store in a cool, dry, well-ventilated area. |

Conditions for safe storage, including any incompatibilities

| | |
|--------------------------------|--|
| Suitable container | <ul style="list-style-type: none"> ▶ Metal can or drum ▶ Packaging as recommended by manufacturer. ▶ Check all containers are clearly labelled and free from leaks. |
| Storage incompatibility | <ul style="list-style-type: none"> ▶ Avoid reaction with oxidising agents |

SECTION 8 Exposure controls / personal protection**Control parameters****Occupational Exposure Limits (OEL)****INGREDIENT DATA**


Not Available

Emergency Limits

| Ingredient | Material name | TEEL-1 | TEEL-2 | TEEL-3 |
|--|---------------|---------------|---------------|---------------|
| PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS) | Not Available | Not Available | Not Available | Not Available |

| Ingredient | Original IDLH | Revised IDLH |
|--|---------------|---------------|
| PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS) | Not Available | Not Available |

MATERIAL DATA**Exposure controls**

| | |
|---|---|
| Appropriate engineering controls | <p>Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this high level of protection. The basic types of engineering controls are:</p> <p>Process controls which involve changing the way a job activity or process is done to reduce the risk.</p> <p>Enclosure and/or isolation of emission source which keeps a selected hazard "physically" away from the worker and ventilation that strategically "adds" and "removes" air in the work environment.</p> |
| Personal protection |  |
| Eye and face protection | <ul style="list-style-type: none"> ▶ Safety glasses with side shields ▶ Chemical goggles. ▶ Contact lenses may pose a special hazard; soft contact lenses may absorb and concentrate irritants. A written policy document, describing the wearing of lenses or restrictions on use, should be created for each workplace or task. This should include a review of lens absorption and adsorption for the class of chemicals in use and an account of injury experience. |
| Skin protection | See Hand protection below |

Continued...

PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS)

| | |
|------------------------------|---|
| Hands/feet protection | Wear general protective gloves, eg. light weight rubber gloves. |
| Body protection | See Other protection below |
| Other protection | No special equipment needed when handling small quantities. OTHERWISE: <ul style="list-style-type: none"> ▶ Overalls. ▶ Barrier cream. ▶ Eyewash unit. |

SECTION 9 Physical and chemical properties

Information on basic physical and chemical properties

| | | | |
|---|---|--|----------------|
| Appearance | Coloured paste with characteristic odour; mixes with water. | | |
| Physical state | Non Slump Paste | Relative density (Water = 1) | <1 |
| Odour | Not Available | Partition coefficient n-octanol / water | Not Available |
| Odour threshold | Not Available | Auto-ignition temperature (°C) | >200 |
| pH (as supplied) | Not Available | Decomposition temperature | Not Available |
| Melting point / freezing point (°C) | >55 | Viscosity (cSt) | Not Available |
| Initial boiling point and boiling range (°C) | Not Available | Molecular weight (g/mol) | Not Applicable |
| Flash point (°C) | >100 | Taste | Not Available |
| Evaporation rate | Not Available | Explosive properties | Not Available |
| Flammability | Not Applicable | Oxidising properties | Not Available |
| Upper Explosive Limit (%) | Not Available | Surface Tension (dyn/cm or mN/m) | Not Available |
| Lower Explosive Limit (%) | Not Available | Volatile Component (%vol) | Not Available |
| Vapour pressure (kPa) | Not Available | Gas group | Not Available |
| Solubility in water | Miscible | pH as a solution (1%) | Not Available |
| Vapour density (Air = 1) | Not Available | VOC g/L | Not Available |

SECTION 10 Stability and reactivity

| | |
|---|--|
| Reactivity | See section 7 |
| Chemical stability | <ul style="list-style-type: none"> ▶ Unstable in the presence of incompatible materials. ▶ Product is considered stable. ▶ Hazardous polymerisation will not occur. |
| Possibility of hazardous reactions | See section 7 |
| Conditions to avoid | See section 7 |
| Incompatible materials | See section 7 |
| Hazardous decomposition products | See section 5 |

SECTION 11 Toxicological information

Information on toxicological effects

| | |
|---------------------|--|
| Inhaled | Acute effects from inhalation of high vapour concentrations may be chest and nasal irritation with coughing, sneezing, headache and even nausea. |
| Ingestion | Ingestion may result in nausea, abdominal irritation, pain and vomiting |
| Skin Contact | Limited evidence exists, or practical experience predicts, that the material either produces inflammation of the skin in a substantial number of individuals following direct contact, and/or produces significant inflammation when applied to the healthy intact skin of animals, for up to four hours, such inflammation being present twenty-four hours or more after the end of the exposure period. Skin irritation may also be present after prolonged or repeated exposure; this may result in a form of contact dermatitis (nonallergic). The dermatitis is often characterised by skin redness (erythema) and swelling (oedema) which may progress to blistering (vesiculation), scaling and thickening of the epidermis. At the microscopic level there may be intercellular oedema of the spongy layer of the skin (spongiosis) and intracellular oedema of the epidermis. |
| Eye | Limited evidence exists, or practical experience suggests, that the material may cause eye irritation in a substantial number of individuals and/or is expected to produce significant ocular lesions which are present twenty-four hours or more after instillation into the eye(s) of experimental animals. Repeated or prolonged eye contact may cause inflammation characterised by temporary redness (similar to windburn) of the conjunctiva (conjunctivitis); temporary impairment of vision and/or other transient eye damage/ulceration may occur. |
| Chronic | Long-term exposure to the product is not thought to produce chronic effects adverse to health (as classified by EC Directives using animal models); nevertheless exposure by all routes should be minimised as a matter of course. |

| | | |
|---|-----------------|-------------------|
| PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS) | TOXICITY | IRRITATION |
| | Not Available | Not Available |

PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS)

Legend: 1. Value obtained from Europe ECHA Registered Substances - Acute toxicity 2. * Value obtained from manufacturer's SDS. Unless otherwise specified data extracted from RTECS - Register of Toxic Effect of chemical Substances

| | | | |
|-----------------------------------|---|--------------------------|---|
| Acute Toxicity | ✗ | Carcinogenicity | ✗ |
| Skin Irritation/Corrosion | ✗ | Reproductivity | ✗ |
| Serious Eye Damage/Irritation | ✗ | STOT - Single Exposure | ✗ |
| Respiratory or Skin sensitisation | ✗ | STOT - Repeated Exposure | ✗ |
| Mutagenicity | ✗ | Aspiration Hazard | ✗ |

Legend: ✗ – Data either not available or does not fill the criteria for classification
 ✔ – Data available to make classification

SECTION 12 Ecological information

Toxicity

| PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976, 218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS) | Endpoint | Test Duration (hr) | Species | Value | Source |
|--|----------|--------------------|---------------|---------------|---------------|
| | | Not Available | Not Available | Not Available | Not Available |

Legend: Extracted from 1. IUCLID Toxicity Data 2. Europe ECHA Registered Substances - Ecotoxicological Information - Aquatic Toxicity 3. EPIWIN Suite V3.12 (QSAR) - Aquatic Toxicity Data (Estimated) 4. US EPA, Ecotox database - Aquatic Toxicity Data 5. ECETOC Aquatic Hazard Assessment Data 6. NITE (Japan) - Bioconcentration Data 7. METI (Japan) - Bioconcentration Data 8. Vendor Data

DO NOT discharge into sewer or waterways.

Persistence and degradability

| Ingredient | Persistence: Water/Soil | Persistence: Air |
|------------|---------------------------------------|---------------------------------------|
| | No Data available for all ingredients | No Data available for all ingredients |

Bioaccumulative potential

| Ingredient | Bioaccumulation |
|------------|---------------------------------------|
| | No Data available for all ingredients |

Mobility in soil

| Ingredient | Mobility |
|------------|---------------------------------------|
| | No Data available for all ingredients |

SECTION 13 Disposal considerations

Waste treatment methods

| | |
|------------------------------|--|
| Product / Packaging disposal | <ul style="list-style-type: none"> ▶ Recycle wherever possible or consult manufacturer for recycling options. ▶ Consult State Land Waste Management Authority for disposal. ▶ Bury residue in an authorised landfill. ▶ Recycle containers if possible, or dispose of in an authorised landfill. |
|------------------------------|--|

SECTION 14 Transport information

Labels Required

| | |
|------------------|----------------|
| Marine Pollutant | NO |
| HAZCHEM | Not Applicable |

Land transport (ADG): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Air transport (ICAO-IATA / DGR): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Sea transport (IMDG-Code / GGVSee): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

Transport in bulk according to Annex II of MARPOL and the IBC code

Not Applicable

SECTION 15 Regulatory information

Safety, health and environmental regulations / legislation specific for the substance or mixture

National Inventory Status

| National Inventory | Status |
|--------------------|--------|
| Australia - AIC | Yes |

**PoliLam Type MWOS Diamond Compound #218-6932, 218-6948, 218-6954, 218-6960, 218-6976,
218-6982, 218-7008, 218-7014, 218-7020, 218-7036, 315-5125 (AUS)**

| National Inventory | Status |
|-------------------------------|--|
| Australia Non-Industrial Use | Yes |
| Canada - DSL | Yes |
| Canada - NDSL | Yes |
| China - IECSC | Yes |
| Europe - EINEC / ELINCS / NLP | Yes |
| Japan - ENCS | Yes |
| Korea - KECI | Yes |
| New Zealand - NZIoC | Yes |
| Philippines - PICCS | Yes |
| USA - TSCA | Yes |
| Taiwan - TCSI | Yes |
| Mexico - INSQ | Yes |
| Vietnam - NCI | Yes |
| Russia - ARIPS | Yes |
| Legend: | Yes = All CAS declared ingredients are on the inventory No = One or more of the CAS listed ingredients are not on the inventory and are not exempt from listing(see specific ingredients in brackets) |

SECTION 16 Other information

| | |
|----------------------|------------|
| Revision Date | 26/08/2020 |
| Initial Date | 26/08/2020 |

Other information

Classification of the preparation and its individual components has drawn on official and authoritative sources as well as independent review by the Chemwatch Classification committee using available literature references.

The SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings. Risks may be determined by reference to Exposures Scenarios. Scale of use, frequency of use and current or available engineering controls must be considered.

Definitions and abbreviations

PC—TWA: Permissible Concentration-Time Weighted Average
 PC—STEL: Permissible Concentration-Short Term Exposure Limit
 IARC: International Agency for Research on Cancer
 ACGIH: American Conference of Governmental Industrial Hygienists
 STEL: Short Term Exposure Limit
 TEEL: Temporary Emergency Exposure Limit.
 IDLH: Immediately Dangerous to Life or Health Concentrations
 OSF: Odour Safety Factor
 NOAEL :No Observed Adverse Effect Level
 LOAEL: Lowest Observed Adverse Effect Level
 TLV: Threshold Limit Value
 LOD: Limit Of Detection
 OTV: Odour Threshold Value
 BCF: BioConcentration Factors
 BEI: Biological Exposure Index

This document is copyright.

Apart from any fair dealing for the purposes of private study, research, review or criticism, as permitted under the Copyright Act, no part may be reproduced by any process without written permission from CHEMWATCH.

TEL (+61 3) 9572 4700.