




Connectors > Pluggable IO Connectors & Cages > zSFP+ Stacked Cage Assembly: Gasket



Form Factor: **zSFP+ Stacked (SFP28)**

Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.8 mm [ .032 in ]**

Sealable: **Yes**

Circuit Application: **Signal**

[All zSFP+ Stacked Cage Assembly: Gasket \(34\)](#)

Features

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP28)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	Yes

Configuration Features

Number of Positions	160
Number of Ports	8
Port Matrix Configuration	2 x 4

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Contact Features

Tail Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]



Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	1.8 mm[.07 in]

Housing Features

Cage Material	Nickel Silver Alloy
Centerline (Pitch)	.8 mm[.032 in]

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	zSFP+ Thermally Enhanced
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-C11-N490111  
SFP28 to SFP28 Cable Assembly: 28 AWG




TE Part # CAT-C11-N4901114  
SFP28 to SFP28 Cable Assembly: 30 AWG




TE Part # 4-2821222-5  
SFP56 DIRECT ATTACH CA, 2M, 30AWG




TE Part # 4-2334985-2  
SFP56 DIRECT ATTACH CA, 1M, 32AWG




TE Part # 2334985-2  
SFP28 DIRECT ATTACH CA, 1M, 32AWG




TE Part # 4-2821224-5  
SFP56 DIRECT ATTACH CA, 3M, 26AWG




TE Part # CAT-Q17-N49011  
QSFP56-Four SFP56 Cable Assembly: 30 AWG




TE Part # CAT-C11-N49011  
SFP28 to SFP28 Cable Assembly: 26 AWG



TE Part # CAT-Q17-N490333  
QSFP56-Four SFP56 Cable Assembly: 26 AWG



TE Part # CAT-C11-N490333  
QSFP28-Four SFP+ Cable Assembly: 30 AWG



TE Part # CAT-C11-N490325  
QSFP28-Four SFP+ Cable Assembly: 26 AWG

Customers Also Bought



TE Part #1-2170287-1  
1X4 CAGE ASSEMBLY, QSFP,SINGLE  
SQ LP

TE Part #1934949-1  
Tinman 5pr 8col vert rcpt 15mm stack

TE Part #1734375-1  
CHAMP .050 HIGH RISE, REVERSED

TE Part #5-1375870-4  
RCPT ASSY,12 POS,VERT,0.8MM MI

TE Part #2132529-3  
IMP100S,H,V3P6C,LG,REW39,5.5

TE Part #1734100-3  
Champ050 series,30pos,Au over PdNi

TE Part #1734101-3  
Champ050 series,30pos,Au over PdNi

TE Part #6-2213362-2  
RCPT ASSY,DIMMABLE  
PHOTOCONTROL,150C,3 P

TE Part #2-6450880-4  
MBXLE R/A RCPT 4P16S4P

TE Part #2007808-2  
IMP100S,H,V4P10C,LG,OEW46,4.9

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-2180324-0\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2180324-0\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2180324-0\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English