

Features

- 50Ω Insulated BNC
- Rugged construction
- Fits standard XLR Ø24mm cutout.
- No soldering or punch termination. Use standard cable for each connector style.
- Front or rear mounted.
- Low rear profile

RS PRO 50Ω Insulated BNC Feedthrough Connector

RS Stock No.: 533-691, 533-693



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

BNC connectors are suitable for a variety of applications including video signalling and test equipment.

Common cabling can be used for front and rear connections. No soldering and no punch terminations - just use the standard cable for that particular connector style.

XLR format feedthrough connectors fit within a standard XLR panel cutout and can be mounted from the front or back. A low rear profile accommodates the tightest behind-the-panel spaces.

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

General Specifications

Connector Type	50Ω BNC
Insulated	Yes

Mechanical Specifications

Frame Material	Zinc Diecast
Frame Finish	Nickel or Black
Mounting hole	Countersink holes
BNC Material	Alloy

Approvals

Standards Met	RoHS
---------------	------

Similar Products

Stock No.	Brand	Product Name	Frame Finish
533-691	RS PRO	50Ω Insulated BNC Connector	Nickel
533-693	RS PRO	50Ω Insulated BNC Connector	Black

