




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.32 – .51 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

--	--



Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	26.4 mm[1.039 in]
Compatible Insulation Diameter Range	1.5 – 2.2 mm[.059 – .087 in]
Terminal Material Thickness	.4 mm[.015 in]
Wire Size	.32 – .51 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on




requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 178025-2 FF 250 CAP HSG DBL 6P BLACK	TE Part # 171445-1 FF 250 TAB HSG 14P ASSY CONN	TE Part # 1-880298-0 FASTON .250 SERIES (6.3 MM) HOUSING	TE Part # 172133-9 FF 250 REC HSG 4P NYLON RED
TE Part # 7-2150978-7 OCEAN_2.0_SPARE_PART_KIT-070F120O	TE Part # 2150978-2 OCEAN-2.0-APPLICATOR-E-070F120O-REA	TE Part # 172384-2 3P CAP HSG	TE Part # 171190-5 FF 250 TAB HSG 6P NYLON RED
TE Part # 172383-2 FF 250 REC HSG 2P NYLON BLCBK P/M	TE Part # 171897-2 FF 250 REC HSG 6P NYLON BLCBK	TE Part # 880638-1 FF 110 TAB 1.0-2.5 MM2 0.40 X 14.1 BR	TE Part # 1-480282-0 FF 250 TAB HSG 6P NYLON BLACK
TE Part # 172133-1 FF 250 CAP HSG 4P NYLON NAT	TE Part # 480053-4 FF 250 TAB HSG 1P NYLON BLACK	TE Part # 480053-5 FF 250 TAB HSG 1P NYLON RED	TE Part # 176773-1 FF 250 CAP HSG 3P NYLON NAT




TE Part # 480116-3
FF 250 TAB HSG 2P NYLON BLACK



TE Part # 172133-4
FF 250 REC HSG 4P NYLON GREEN



TE Part # 180916-1
FF 250 TAB HSG 1P NYLON RED



TE Part # 926097-1
FF 250 TAB HSG 3P NYLON NAT

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(195)



Insertion & Extraction Tools(2)



Quick Disconnects(216)

Customers Also Bought



TE Part #1747066-3
GRACE INERTIA CONN 2.5 PLUG
HSG 3P NATUR



TE Part #1376106-1
025 CONN CAP ASSY 16P




TE Part #1380088-1
PL MKIII .250 REC 0.5-1.0MM2




TE Part #4-280050-1
250 FASTON,FLAG,REC.,16-20 AWG,
BR




TE Part #881339-1
SLEEVE FOR .250 SRS FASTON TAB



TE Part #444334-1
250 FASTON REC 22-18 AWG BR



TE Part #216030-000
55A0111-24-6



TE Part #929966-1
STIFTKONTAKT 2,5MMD



TE Part #1-180984-2
FASTON 250 BOOT NYLON BLK



TE Part #2-1747066-4
GRACE INERTIA CONN 2.5 PLUG
HSG 4P BLUE



Documents

Product Drawings

FF 250 TAB 22-20AWG BR WITHOUT LATCH

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170349-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170349-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170349-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of 250 Series Tab and Receptacle Contacts

Japanese

Application Specification

Japanese

Application Specification

Japanese

Crimping of 250 Series Tab and Receptacle Contacts

Japanese

Instruction Sheets

Customer Manual (non U.S.)

Japanese

"250" Series, Housing Lance Connector

Japanese