
BES 516-324-E4-C-PU-03 BES00N5

BALLUFF



CE

- PNP
- Normally open (NO)
- 1.50 mm
- Flush (shielded)
 Cable, PUR, 3.00 m

General attributes Approvals / Conformity

cULus EAC Basic standard IEC 60947-5-2

Enclosure Type per IEC 60529 Function indicator IP68 according to BWN PR 20 Yes Polarity reversal protected Yes Power indicator No Protection Class Short circuit protected Yes MTTF (40°C) 830 a

Electrical attributes

Connection type Eff. operating current le Cable 200 mA Eff. operating voltage Ue DC 24.0 V Electrical version Load capacitance max. (at Ue) DC, direct current 0.500 μF Max. no-load cur. lo undamped Minimum operating current Im No-load current lo damped max. 3.0 mÅ 0 mA 9.0 mA Operating voltage UB max. DC [V]
Operating voltage UB min. DC [V]
Rated insulation voltage Ui 30.0 V 10.0 V 250 VAC Rated short circuit current Ripple max. (% of Ue) 100 A 15 % Switching freq. f max. (at Ue)

3000 Hz Switching function Normally open (NO) PNP Switching output

BN BK BU









IND. CONT. EQ
81U2
US for use in the secondary of a class 2 source of supply
Environmental - Type 1 Enclosure



2.5 V

PBT

8 Nm

Voltage drop static max.

Mechanical attributes
Ambient temperature Ta max. 70 °C -25 °C 1.20 mm Ambient temperature Ta min. Assured operating distance Sa Cable diameter D max. 3.1 mm Cable jacket material PUR 3.00 m 0.14 mm² Cable length Conductor cross-section Depth 30.0 mm Diameter d1 M08x1 Eff. operating distance Sr 1.50 mm Housing material Stainless steel Mech. installation condition Flush (shielded) Mounting length 29.0 mm Number of conductors Rated operating distance Sn [mm] Sensing face material 1.50 mm

Tightening torque

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.