

Product data sheet

Specifications



Repacked, auxiliary contact, Acti9 iC60 RCBO, 1 OF/SD, AC/DC

A9A19803W



This repacked option saves 0.005 over the standard condition

Main

range of product	Acti9
Product or component type	OC or fault contact
Device short name	iOF/SD
Signal contacts composition	1 C/O
[In] rated current	6 A at 24 V, DC 2 A at 60 V, DC 1.5 A at 110 V, DC 1 A at 250 V, DC 6 A at 24...230 V, AC 50 Hz 3 A at 415 V, AC 50 Hz
9 mm pitches	1
Standards	EN/IEC 60947-5-1

Complementary

Range compatibility	Acti9 iC60 RCBO
Mounting mode	Clip-on
Mounting support	DIN rail
Height	86 mm
Width	9 mm
Depth	71 mm
Product weight	36 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom): 1 cable(s) 0.25...4 mm ² - rigid Screw clamp terminal (bottom): 1 cable(s) 0.25...2.5 mm ² - flexible Screw clamp terminal (bottom): 2 cable(s) 1.5 mm ² - rigid Screw clamp terminal (bottom): 2 cable(s) 1.5 mm ² - flexible Screw clamp terminal (bottom): 1 cable(s) 2.5 mm ² - flexible with ferrule
Wire stripping length	6 mm for bottom connection
Tightening torque	0.6 N.m bottom

Environment

Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8.5 cm
Package 1 Length	10.4 cm
Package 1 Weight	52 g
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.286 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A7b24ae6-2312-4e67-b7c9-56fce3e8c723

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins