

Control cabinet feed-through - VS-BH-M12FS-8CON-RJ45/ 90 - 1405057

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Control cabinet feed-through, M12, 8-pos., A-coded on RJ45 socket, socket input 90°, IP65/67

Product Features

- ✓ 1 Gbps
- ✓ IP65/67



Ethernet Ethernet

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	36.8 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP65
	IP67

General

Rated current at 40°C	1 A
Rated voltage	50 V
Number of positions	8
Signal type/category	Ethernet CAT5 (IEC 11801:2002), 1 Gbps
Insertion/withdrawal cycles	≥ 100

Material

Flammability rating according to UL 94	V0
Contact material	Copper alloy

Control cabinet feed-through - VS-BH-M12FS-8CON-RJ45/ 90 - 1405057

Technical data

Material

Material of grip body	PA
-----------------------	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27279220
eCl@ss 7.0	27440103
eCl@ss 8.0	27440103

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Control cabinet feed-through - VS-BH-M12FS-8CON-RJ45/ 90 - 1405057

Approvals

Approvals submitted

Approval details

EAC


EAC

Drawings

Explosion drawing


Dimensional drawing

Exploded drawing



Panel cutout

Dimensional drawing



Panel cutout