

Parker Product Datasheet



Parker Legris compact needle valves can be installed in any system and are designed for applications requiring accurate leak-free fluid control and excellent service life.

PART NUMBER: 0531 04 10
SHAPE: Right angle needle valve male and female
BODY MATERIAL: NICKEL PLATED BRASS
PRODUCT TYPE: Brass Needle Valves
CONNECTION 2 TUBE O.D. (MM): na
DIAMETER NOMINAL (DN): 4
CONNECTION 1 THREAD SIZE (METRIC): G1/8
CONNECTION 1 THREAD STYLE: BSPP

PRODUCT OVERVIEW

Parker Legris compact needle valves can be installed in any system and are designed for applications requiring accurate leak-free fluid control and excellent service life.

Features/Benefits:

- Robust and Easy-to-Use
- Accurate flow control
- Forged brass for improved long-term mechanical strength
- Robust stem for good operational reliability
- Corrosion resistance

- Wide range

- Two materials (nickel-plated brass and stainless steel) suitable for many applications
- Numerous valve and safety accessory configurations

Markets:

- Packaging
- Wearing Apparel
- Lumber & Wood
- Rubber & Tire Processing
- Plastic Processing
- Water
- Rail

Applications:

- Allow/Stop Fluid Circulation on Industrial Circuits with Accuracy
- Suitable for Slightly Corrosive Industrial Fluids

Technologies:

- Pressure relief valve
- Industrial valves
- Gauge valve
- Brass needle valve
- Stainless steel needle valve

Technical Characteristics:

- Fluids:

Brass: Compressed air, water, industrial fluids, etc. Other fluids: contact us

Stainless steel: Many fluids

- Materials: zamk, nickel-plated brass or 316L stainless steel, mineral fibre, nickel-plated shot-blasted brass or stainless steel, silicone free

- Pressure:

Brass: 0 to 120 bar

Stainless steel: 0 to 400 bar

- Temperature:

Brass: -20°C to +100°C (except model 0510)

Stainless steel: -20°C to 180°C

Regulations:

- DI: 97/23/EC (module PED A - diameters greater than 25 mm)
- DI: 2006/42/EC (Machinery Directive)
- DI: 2002/95/EC (RoHS)
- RG: 1907/2006 (REACH)

Product Types:

- In-Line Needle Valve, Female BSPP Thread
- In-Line Needle Valve, Male/Female BSPP Thread
- In-Line Needle Valve with Compression Connections
- Right-Angle Needle Valve, Female BSPP Thread
- Right-Angle Needle Valve, Male/Female BSPP Thread
- Needle Drain Valve, Male BSPP and Metric Thread
- Needle Drain Valve, Male NPT Thread
- Automatic Vent Pressure Gauge Valve, Female BSPP Thread
- Pressure Relief Valve, Male BSPP Thread
- Needle Valve, Female BSPP Thread

TECH SPECIFICATIONS

MAXIMUM OPERATING TEMPERATURE	100 °C
MAXIMUM OPERATING TEMPERATURE	212 °F
DIVISION	Low Pressure Connectors Europe Division
DIVISION	Low Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	1740 psi
MAXIMUM OPERATING PRESSURE	120 bar
MAXIMUM OPERATING PRESSURE	12 MPa
FLOW RATE	6.98 to 22.98 NL/min at 6 bar (H2O)

MINIMUM OPERATING TEMPERATURE	-20 °C
MINIMUM OPERATING TEMPERATURE	-4 °F
FOR FLUID TYPE	Water
FOR FLUID TYPE	Inert Gases
FOR FLUID TYPE	Air
FOR FLUID TYPE	Oil
INDUSTRY	Industrial Manufacturing Equipment
SPECIFICATIONS MET	DI: 97/23/EC (module PED A - diameters greater than 25 mm)
REGION OF ORIGIN	France
CONNECTION TYPE	BSPP
APPLICATION	Water Circuits
APPLICATION	Pneumatics
APPLICATION	Textile
APPLICATION	Machine Tools
APPLICATION	Rubber Industry
APPLICATION	Packaging
BRAND	Legris
TECHNOLOGY	Pneumatics
TECHNOLOGY	Fluid & Gas Handling
TECHNOLOGY	Process Control
CONNECTION SIZE	G1/8
PRODUCT STYLE	Male and Female Needle Valve
BODY MATERIAL	Nickel-Plated Brass
PRODUCT SERIES	Brass Needle Valves
PRODUCT TYPE	Needle Valves

SLEEVE MATERIAL	Brass
SEAL MATERIAL	Mineral Fiber
WEIGHT	0.082 kg
WEIGHT	0.1804 lb
MAXIMUM FLOW RATE	22.98 NL/min at 6 Bar (H2O)
MAXIMUM FLOW RATE	6.98 NL/min at 6 Bar (H2O)
MOUNTING TYPE	Inline
FUNCTION	2-way
ACTUATION TYPE	Manual
ORIFICE SIZE	4 mm
CYCLES PER LIFETIME	n/a
OPERATION TYPE	Lever-operated
CONFIGURATION	n/a
SEAT MATERIAL	n/a
HANDLE TYPE	Butterfly Lever (Nickel-Plated Brass)
QUANTITY PER BOX	1
NUMBER OF PORTS	n/a