

VL3 UPC 1110 - Box PC



1433148

<https://www.phoenixcontact.com/gb/products/1433148>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Compact IP30-rated, fanless industrial box PC (BPC) with efficient, long-term available Intel Atom® x6211E processor with 2 GB LPDDR4 RAM and 30 GB NVMe SSD onboard storage.

Commercial data

Item number	1433148
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRBAAA
Product key	DRBAAA
GTIN	4063151799854
Weight per piece (including packing)	1,060 g
Weight per piece (excluding packing)	700 g
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
--------------	--------

Computer data

Processor	Intel® Atom® x6211E, Number of cores: 2 x 1.3 GHz
Trusted Platform Module	dTPM 2.0, Infineon® SLB9670 (Encryption technology not Chinese)
Operating system	without operating system
RAM	2 GB DDR
Data storage system	30 GB, 3D TLC (onboard)
Cooling	passive
Raid system	without RAID system

Display

MTBF	59,230 hours at 60°C
------	----------------------

System properties

Processor	Intel® Atom® x6211E, Number of cores: 2 x 1.3 GHz
-----------	---

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage	24 V DC 20 %
Max. current consumption	2.08 A (24 V DC)
Typical current consumption	0.58 A (24 V DC)

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Connection data

Power supply

Connection method	Push-in spring connection
Conductor cross section, rigid	0.2 mm² ... 1.5 mm²
Conductor cross section, flexible	0.2 mm² ... 1.5 mm²
Conductor cross section AWG	24 ... 16
Stripping length	10 mm

Interfaces

VL3 UPC 1110 - Box PC



1433148

<https://www.phoenixcontact.com/gb/products/1433148>

Interfaces	2x USB 3.1 Gen.1 - Type A
Monitor output	1x DP++ 1.4
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® i225-IT

Dimensions

External dimensions

Width / Height / Depth	100 mm / 50 mm / 100 mm (Housing dimensions)
------------------------	--

Material specifications

Housing material	Aluminum / steel sheet DC01
------------------	-----------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-20 °C ... 60 °C (0...2000 m altitude, with 0.5 m/s air flow) -20 °C ... 54 °C (2001 ... 3000 m altitude, with 0.5 m/s air flow)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	3000 m (above sea level)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	UL 61010-1, UL 61010-2-201 Class I, Div. 2, Groups A, B, C, D T4

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

VL3 UPC 1110 - Box PC



1433148

<https://www.phoenixcontact.com/gb/products/1433148>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1433148>

	IECEE CB Scheme Approval ID: US-43772-M1-UL
	cULus Listed Approval ID: E238705 D16:D1058
	cULus Listed Approval ID: US-UL-2412129-2

VL3 UPC 1110 - Box PC

1433148

<https://www.phoenixcontact.com/gb/products/1433148>



Classifications

ECLASS

ECLASS-13.0	19200102
-------------	----------

ETIM

ETIM 9.0	EC001413
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b0d356b7-8ffa-412f-a1df-710a81dfca4d