





Standard

Tel: 0121 789 8686

Email: heatsinks@ablcomponents.co.uk



Stock Category	
A	stocked item short lead time
B	lead times vary
C	Minimum Order Quantities apply

Model	Width [mm]	Length [mm]	Height [mm]	Anodised Finish	Thermal Tape	Pad Size [mm]	Wire Form	°C/W Natural	°C/W Forced 2M/s	Stock Caty	Pin Length [mm]	Pin Pitch L / W [mm]	Hole Dia [mm]
BGA-STD-010	13.5	13.0	10.0	Black	Y	12x12	-	27.00	14.50	A	n/a	n/a	n/a
BGA-STD-015	14.0	14.0	10.0	Black	Y	12x12	-	26.50	14.00	A	n/a	n/a	n/a
BGA-STD-020	21.0	21.0	9.0	Black	Y	20x20	-	24.50	13.00	A	n/a	n/a	n/a
BGA-STD-025	23.0	23.0	6.0	Black	Y	20x20	-	22.00	10.50	A	n/a	n/a	n/a
BGA-STD-030	27.0	27.0	6.0	Black	Y	20x20	WF700/WF300	20.00	10.00	A	n/a	n/a	n/a
BGA-STD-035	26.0	26.0	8.0	Black	Y	20x20	WF700/WF300	18.50	9.70	A	n/a	n/a	n/a
BGA-STD-040	27.0	27.0	6.0	Black	Y	20x20	WF700/WF300	16.00	10.20	A	n/a	n/a	n/a
BGA-STD-045	23.0	23.0	18.0	Black	Y	20x20	WF700/WF300	14.70	7.30	A	n/a	n/a	n/a
BGA-STD-050	20.0	20.0	19.1	Black	Y	18x18	-	14.00	5.80	A	n/a	n/a	n/a
BGA-STD-055	25.9	23.9	10.0	Black	Y	20x20	WF700/WF300/WF151	14.00	6.00	A	n/a	n/a	n/a
BGA-STD-060	40.0	40.0	10.0	Black	Y	30x30	-	13.50	7.50	A	n/a	n/a	n/a
BGA-STD-065	27.8	27.8	11.2	Black	Y	20x20	WF700/WF300	12.20	5.80	A	n/a	n/a	n/a
BGA-STD-070	40.0	40.0	25.0	Black	Y	30x30	WF700/WF300/WF151	11.50	6.00	A	n/a	n/a	n/a
BGA-STD-075	40.0	40.0	23.0	Black	Y	18x18	WF700/WF300/WF151	11.00	5.60	A	n/a	n/a	n/a
BGA-STD-080	27.0	27.0	25.0	Black	Y	20x20	WF700/WF300/WF151	10.50	4.50	A	n/a	n/a	n/a
BGA-STD-085	30.7	30.7	14.1	Black	Y	20x20	WF700/WF300	10.00	5.20	A	n/a	n/a	n/a
BGA-STD-090	40.0	23.9	10.0	Black	Y	20x20	-	10.00	5.20	A	n/a	n/a	n/a
BGA-STD-095	40.0	40.0	10.0	Black	Y	18x18	WF700/WF300	9.70	4.00	A	n/a	n/a	n/a
BGA-STD-100	38.1	38.1	16.0	Black	Y	30x30	-	9.20	4.10	A	n/a	n/a	n/a
BGA-STD-105	35.0	35.0	18.0	Black	Y	30x30	WF700/WF300/WF151	9.20	5.20	A	n/a	n/a	n/a
BGA-STD-110	35.0	35.0	25.0	Black	Y	30x30	WF700/WF300/WF151	8.50	5.00	A	n/a	n/a	n/a
BGA-STD-115	40.0	40.0	18.0	Black	Y	30x30	WF700/WF300/WF151	8.20	5.10	A	n/a	n/a	n/a
BGA-STD-120	40.6	38.8	30.5	Black	Y	30x30	-	7.00	3.70	A	n/a	n/a	n/a

Thermal Resistance is calculated based on a distributed heat load on anodised heatsink with vertically mounted fins based on a 60°C temperature rise. Under general operating conditions the thermal mounting arrangement of devices is not known and therefore the figures should be used only as a guide to selection. We recommend that the effectiveness of any heat sink is tested in the specific operating environment in which it will be subjected. All information is for reference purposes only.