


06110030

RCK 11 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06110030
Ød (DD) mm	30
ØD (D) mm	55
L1 (L1) mm	32
L2 (L2) mm	40
L (L) mm	46
Maximum torque Mt (MT) N/mm ²	1000
Clamping pressure - Shaft (CPS) N/mm ²	246
Clamping pressure - Hub (CPH)	134
Clamping pressure - N° (CPN)	6
Clamping screws DIN 912 MAT. 12.9 - Type (CSTY) mm	M6x35
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTO)	17
Extraction thread - Type (ETT) mm	M6
Extraction thread - N° (ETN)	3
Weight (WEIGHT) kg	0.60