

## 1.31/2

### Internal extractor set

Code	ETIM
<b>8014880</b>	<b>EC011834</b>
EAN	UNSPSC
<b>4036976105445</b>	<b>27-11-17-12</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-15-01</b>
Customs tariff number	
<b>82055980</b>	



### Article description

- Sets comprise the most used extractor sizes for the removal of ball bearings, bearing races, bushings, shaft seals, etc.
- In robust sheet metal case

### Article parts list

1.30/2 Internal extractor 12-15 mm, 1.30/3 Internal extractor 15-19 mm, 1.30/4 Internal extractors 19-25 mm, 1.30/4A Internal extractors 25-30 mm, 1.30/5 Internal extractors 30-35 mm, 1.30/6 Internal extractors 35-45 mm, 1.30/7 Internal extractor 45-55 mm, 1.30/8 Internal extractor 55-70 mm, 1.36/1 Counter support for 1.30/0 - 1.30/5, 1.36/2 Counter support for 1.30/6 - 1.30/7, 1.31/299B Sheet metal box empty

### Article information

Contents (Qty of pieces)	<b>10</b>	Spindle anti-slip device	<b>no</b>
Version/Execution	<b>In a handy tin box</b>	Screws included	<b>no</b>
Graduation	<b>no</b>	Anti-slip device on the spindle	<b>no</b>
reversible arms available	<b>no</b>	Exchangeable spindle tip	<b>no</b>
Clamping bracket available	<b>no</b>	Can be retrofitted with hydraulic spindle	<b>no</b>
Net weight [kg]	<b>9,2 kg</b>	Total length [mm]	<b>460 mm</b>
Hook brake available	<b>no</b>	Total width [mm]	<b>240 mm</b>
Hook can be moved parallel	<b>no</b>	Total height [mm]	<b>65 mm</b>
Quick release lever available	<b>no</b>	Clamping width $a_2$ (min.) internal pulling [mm]	<b>12 mm</b>
3D data available	<b>no</b>	Clamping width $a_2$ (max.) internal pulling [mm]	<b>70 mm</b>