

## FEATURES

- **4 Pin Pole Format:** Supports multiple connections for versatile use
- **IP67 Rating:** Provides excellent protection against dust and water ingress
- **Gold-Plated Brass Contacts:** Ensures reliable conductivity and corrosion resistance
- **Bayonet Mating Type:** Allows for quick and secure connections
- **Wide Operating Temperature Range:** Functions effectively from -20 °C to 70 °C
- **Screw Termination:** Facilitates easy and secure wiring
- **Durable Housing Materials:** Made from 66 Nylon and Polycarbonate for enhanced durability

## RS PRO SY25 Circular Connector, 4 Pin

RS Stock No: 672-250



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO SY25 Circular Connector is a versatile and robust solution for secure electrical connections in demanding environments. Designed for both industrial and commercial applications, this connector offers reliable performance with a current rating of 10 A and a voltage capacity of 500 V. Its bayonet mating type ensures quick and secure connections, making it ideal for applications where frequent disconnection is required.

## General Specifications

Contact Gender	Female/Male
Contact Material	Brass
Contact Plating	Gold
Mating Type	Bayonet
Number of Contacts	4
Orientation	Straight
Product Type	Circular Connector
Connector Size	SY25
Current	10 A
Housing Material	66 Nylon, Polycarbonate
Termination Type	Screw

## Protection Category

IP Rating	IP67
-----------	------

## Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-20 °C

## Mechanical Specifications

Mount Type	Solder
------------	--------

## Electrical Specifications

Plug/Socket	Plug, Socket
Pole Format	4 Pin
Voltage	500 V

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, CE, RoHS
---------------------	--------------------------------