



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Black**
Primary Product Material: **PBT GF**
Automotive Connector Accessory Type: **Housing**
Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Housing
-------------------------------------	---------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Compatible With Agency/Standards Products	NFR, VDA
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Method	Package
Packaging Quantity	3000

Other

Serviceable	No
-------------	----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP Auto Squib Products



Automotive Connector Caps & Covers (2)	Automotive Housings(12)	Automotive Terminals(1)	Connector Contacts(1)
Other Automotive Connector Accessories(19)	PCB Headers & Receptacles(1)	Power Contacts(1)	

Customers Also Bought

TE Part #1-1823640-1 SHORT CIRC PLUG,AK2,ASSY	TE Part #1-1703884-3 2POS,SHORT CIRC SPR,HOUSING,AS	TE Part #2-1823640-1 SHORT CIRC PLUG,AK2,ASSY	TE Part #1-1703885-1 2POS,SHORT CIRC SPR,HOUSING
TE Part #2-1703884-1 2POS,SHORT CIRC SPR,HOUSING, ASSY	TE Part #1473369-5 SQUIB 11DIA SCR ASSY 8.8MM TYP	TE Part #1473369-1 SQUIB 11DIA SCR ASSY 8.8MM TYP	TE Part #2-1703885-1 2POS,SHORT CIRC SPR,HOUSING
TE Part #1376766-1 SQUIB 11DIA SCR ASSY 9.3MM TYP	TE Part #1376766-3 SQUIB 11DIA SCR ASSY 9.3MM TYP		

Documents



Product Drawings

2POS,SHORT CIRC SPR,HOUSING,ASSY

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1703884-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1703884-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1703884-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

product-1-1703884-1.datasheet

English