

Features

- Ball bearing hub type
- Polypropylene (PP) hub material
- Load capacity of 200 kg
- Threaded-stem mounting type
- Overall height of 58 mm
- Swivel rotation
- Stem diameter of 10 mm
- Stem height of 20 mm

RS PRO AGILA

RS Stock No.: 183-0091



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, socket head cap screw, loose fitted. Wheel centre made of steel, Tread: Polyurethane, casted, precision ball bearing.*

General Specifications

Wheel diameter	35 mm
Width of Tread	25 mm
Threaded stem	10 x 20 mm
Offset	13.5 mm
Swivel Interference	62 mm
Swivel Radius	31 mm
Hardness of tread	Shore D 42
Load capacity	100 kg
Load capacity (static)	200 kg

Mechanical Specifications

Weight	0.243 kg
Overall height	58 mm

Approvals

Standard	EN 12530
----------	----------

