



REVISIONS				
REV	DESCRIPTION	DATE	DWN	APVD



FONT TYPE : Gotham
• LETTER SPACING : 0
• COLOR : Laser Engraving
(Base material color)



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
2. DIMENSIONS APPLY AFTER FINISHING.
3. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
4. ELECTRICAL DATA SHOWN FOR REFERENCE ONLY. SEE LINX DATA SHEET FOR COMPLETE ELECTRICAL PROPERTIES.
 1. ANTENNAS QUALIFIED IAW 108 TEST PLAN AT LATEST REVISION.
 2. IMPEDANCE: 50Ω
 3. CONNECTOR: SMA TYPE INTERFACE IAW MIL-STD-348B
 4. FREQUENCY: MULTI-BAND [SEE DATASHEET]
 5. VSWR NTE 3.3 THROUGH ALL LTE BANDS
5. PACKAGE UNIT INDIVIDUALLY BEFORE PLACING IN LOT BAG.
6. WEIGHT 10g.
7. OPERATING TEMP: -40°- +130°C

7. OPERATING TEMP. -40°-+150°C		DWN		10/17/19	MATERIAL		FINISH		—							
DIMENSIONS: mm		SHOGAN		10/17/19	TE Connectivity											
		CHK		10/17/19												
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±3 ±2 ±1 ±5 ±- ±30'°		CLEWIS		10/17/19	NAME ANTENNA LTE MON SMA POSITIONABLE											
		APVD		10/17/19												
		DASARATHAN														
		PRODUCT SPEC														
		—			SIZE A4											
		APPLICATION SPEC														
		—														
		WEIGHT		—	CAGE CODE		DRAWING NO		RESTRICTED TO							
					00779		C=L001267-01									
CUSTOMER DRAWING					SCALE		1:1		SHEET		1 OF 1		REV		1	