Parker Product Datasheet



Parker Parkrimp Medium Pressure Fittings - 48 Series - are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers.

PART NUMBER: 1CF48-10-5C
PRODUCT STYLE: -
HOSE INSIDE DIAMETER: -5
SHAPE: Elbow 90°
PORT TYPE: DKOL
BODY MATERIAL: Stainless Steel
PORT SIZE: 10 mm
CONNECTION 2 TYPE: Female Metric L - Swivel (24° Cone with O-Ring)

PRODUCT OVERVIEW

Parker's Parkrimp No-Skive medium pressure fittings 48 series are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers. Assembly of No-Skive hose and fittings does not require removal of the outer cover of the hose. This eliminates premature hydraulic hose failure caused by skiving too long or short. 48 series fittings have chromium-6-free plating and are used with Parker wire braided hydraulic hoses such as Global Core with standard, tough or super tough cover, Elite No-Skive with standard, tough or super tough cover, No-Skive Compact water cleaning hoses, No-Skive Compact Rail Hoses with fire retardant cover, hydraulic hoses according EN 853 1SN / SAE 100R1AT, EN 853 2SN / SAE100R2AT, suction and return hoses according SAE 100R4, and a lot more.
Parker Hannifin also meets the requirements of SAE J1273 and ISO 17165-2, which pay particular attention to matching the hose with the fittings and to their compatibility proven by the manufacturer.

Markets:
· Construction Equipment
· Injection Moulding
· Transportation
· Forestry and Agriculture

· Materials Handling
· Pulp and Paper

Features / Benefits:
· Matched hose und fitting system guarantees an approved and safe combination and the highest quality and safety combined with the longest service life of the final product to the end-users.
· No-Skive technology offers the easiest and most efficient and safe production process to the assemblers.

Applications:
· All construction equipment machines
· Large injection moulding machines
· Agriculture and forestry machines
· Container handling machines
· High pressure cleaners
· Paper machines

Parker Parkrimp medium pressure fittings - 48 series are compatible with the following hoses:
· 301SN, 301TC
· 304
· 387, 387TC and 387ST
· 421SN, 421RH
· 426 and 436
· 441 and 441RH
· 451TC
· 461LT
· 462, 462CLF, 462TC and 462ST
· 471TC
· 477 and 477ST
· 487, 487TC and 487ST
· 493
· 811

TECH SPECIFICATIONS

FOR FLUID TYPE	Hydraulic Fluids
CONNECTION 2 TYPE	Swivel

SPECIFICATIONS MET	ISO 12151-2-SWE-L
CONNECTION 2 TYPE	Female
INDUSTRY	Transportation
TECHNOLOGY	Fluid & Gas Handling
CONNECTION LENGTH	37 mm (see drawing legend B)
CONNECTION 1 SIZE	5/16 inch Hose I.D.
DROP LENGTH	30 mm (see drawing legend E)
CONNECTION 2 SIZE	M16x1.5 mm Thread
FOR FLUID TYPE	Air
SHAPE	Elbow 90°
CONNECTION 1 TYPE	Hose
FOR FLUID TYPE	Coolants (Water-Glycol)
CONNECTION 1 SIZE	7.9 mm Hose I.D.
APPLICATION	Hydraulics
COATING	Chromium 6 Free-plated
INDUSTRY	Off-road Machinery
PRODUCT TYPE	Hose Fittings
CONFIGURATION	Hose to Port
INDUSTRY	Industrial Manufacturing Equipment
FOR FLUID TYPE	Water
TUBE OUTSIDE DIAMETER	10 mm
BRAND	Parker
HEX SIZE	19 mm (see drawing legend W)
FOR FLUID TYPE	Mineral Hydraulic Oil
BODY MATERIAL	Stainless Steel
CONNECTION 2 TYPE	Metric L
DIVISION	Polymer Hose Division Europe

MAXIMUM OPERATING PRESSURE	400 bar
PORT TYPE	DKOL
CONNECTION 1 SIZE	-5 (Size)
MAXIMUM OPERATING PRESSURE	40.0 MPa
FITTING LENGTH	61 mm (see drawing legend A)
CONNECTION 2 TYPE	24° Cone (with O-Ring)
DIVISION	Polymer Hose Division Europe