


1224.E - Worksite-maintenance fixed vices



Description:

- Vices in spheroid graphite cast iron, tensile strength 700 N/mm² minimum.
- Wide bearing base of the prism guide/mobile jaw: lack of guide flexion, vice operation preserved even under heavy loads.
- Interchangeable parallel jaws. High wear resistance, hardness 48/53 HRc.
- Removable V-shaped jaws for tightening the pipes. Hardness 40/46 HRc.
- Adjustment system by 2 complex gap compensation screws.
- Burnished control bar.

	Length L [mm]	Length L1 [mm]	Length L2 [mm]	Length L3 [mm]	Head Width B [mm]	Height H [mm]	Height H1 [mm]	A Maxi [mm]	Weight [Kg]
1224.100E	345.0	104.0	51.0	70.0	63.0	142.0	74.0	125.0	8.67
1224.125E	380.0	127.0	53.0	76.0	75.0	156.0	83.0	150.0	11.34
1224.150E	460.0	154.0	60.0	91.0	95.0	183.0	94.0	200.0	17.26
1224.175E	532.0	178.0	68.0	111.0	118.0	216.0	123.0	235.0	24.68