



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Centerline (Pitch): **.5 mm**

Mating Retention Type: **Zero Insertion Force (ZIF)**

PCB Mount Orientation: **Right Angle**

Contact Mating Location: **Dual Side**

Termination Method to PCB: **Surface Mount**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| PCB Connector Type                | PCB Mount Receptacle  |
| Connector & Contact Terminates To | Printed Circuit Board |
| Connector Product Type            | Connector Assembly    |
| Connector System                  | Wire-to-Board         |
| FPC Actuator Type                 | Back Flip-Lock        |

Configuration Features

|                                   |             |
|-----------------------------------|-------------|
| Compatible With Wire & Cable Type | FFC, FPC    |
| Number of Rows                    | 1           |
| PCB Mount Orientation             | Right Angle |
| Number of Positions               | 8           |

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 50 VDC |
|-------------------|--------|

Body Features

|                       |         |
|-----------------------|---------|
| Primary Product Color | Natural |
| Actuator Color        | Black   |

Contact Features

|                              |               |
|------------------------------|---------------|
| Contact Current Rating (Max) | .5 A          |
| Contact Shape & Form         | Standard Flat |



|                                               |              |
|-----------------------------------------------|--------------|
| Contact Layout                                | Inline       |
| Contact Base Material                         | Copper Alloy |
| PCB Contact Termination Area Plating Material | Gold         |
| Contact Mating Location                       | Dual Side    |
| Contact Mating Area Plating Material          | Gold Flash   |

Termination Features

|                           |               |
|---------------------------|---------------|
| Termination Method to PCB | Surface Mount |
|---------------------------|---------------|

Mechanical Attachment

|                       |                            |
|-----------------------|----------------------------|
| Mating Alignment      | With                       |
| Mating Retention Type | Zero Insertion Force (ZIF) |

Housing Features

|                    |                              |
|--------------------|------------------------------|
| Housing Material   | LCP (Liquid Crystal Polymer) |
| Centerline (Pitch) | .5 mm                        |

Dimensions

|                              |               |
|------------------------------|---------------|
| Accepts Flex Cable Thickness | .3 mm[.01 in] |
| Connector Height             | 1 mm[.039 in] |
| Connector Length             | 6 mm          |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |
|-----------------------------|---------------------------|

Packaging Features

|                  |             |
|------------------|-------------|
| Packaging Method | Tape & Reel |
|------------------|-------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC                                                 |



Free

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-2328702-0  
50 PIN 0.5MMP FPC CONN, BACK  
FLIP LOCK

Customers Also Bought

TE Part #2344044-1  
2 PORT HDR SEALED MATENET  
ASSY, COD A/B

TE Part #2180324-6  
zSFP+ STACKED 2X4 RECEPTACLE  
ASSEMBLY

TE Part #2007637-7  
SFP+ assy 2x2 spring Fingers Outer Lp  
Sn



TE Part #2118909-2  
PCB Ant, MHF, 268.8mm, Wi-Fi 6E  
Triple

TE Part #4-2176328-9  
CRGP 1206 100K 1%

TE Part #5-2176398-0  
3502 1M5 1%

TE Part #2273034-1  
M12 x 1.0 straight plug pigt A

TE Part #6368011-1  
STK MJ,2X1,SHLD,G/G/G/G LEDs



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2328702-8\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2328702-8\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2328702-8\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773959-7-FPC-Connectors-CN

English

Product Specifications

Product Specification

English

Product Specification

English