

Festo Essentials

Featuring products from the Festo 🛨 CORE Program

Readily available • Quick delivery • Great value













Your first choice products for simple, cost-effective pneumatic control

Mini slide DGST



The most compact of its kind on the market, but big in performance and precision

A real space-saver: the compact and short slide unit features integrated cushioning components and sensor mounts. The mini slide delivers maximum precision across the entire stroke thanks to the combination of yoke and slide in one part and the recirculating ball bearing guide underneath it. The large range of cushioning options together with the use of position transmitters opens up numerous applications.

Areas of application

- Pick and Place handling units.
- Piggyback handling units.
- Precise positioning.
- Precise press-fitting.

Cushioning

- Elastic cushioning at both ends, no end-position adjustment.
- Elastic cushioning at both ends, non-adjustable, with end-position adjustment.
- Shock absorbers at both ends, self-adjusting, with end-position adjustment.

Suitable industries

- Electronics and light assembly.
- Machine building.
- Handling technology.

Guided drive DFM



A true guiding light!

Robustness is the name of the game with the DFM. This impressive guided drive has the best price/performance ratio in the market and offers optimum guide characteristics, sturdiness and flexibility. It is reliable, adaptable and resilient — even with high torques. The combination of linear drive and powerful guide in a compact unit means that the DFM can reliably move high loads, even in tight spaces.

Areas of application

- Excellent operational stability compared to standard drives.
- High resistance to torques and lateral forces.
- Good for tasks involving clamping, stopping, pushing, pulling, restraining, holding, cutting, stopping and separating.

Compact cylinder ADN-S



The smallest compact cylinder for micro movements

The compact cylinder series ADN-S is optimized in terms of installation space. Its strong point is its design, which is ideal for simple pressing and holding functions in relatively clean environments. In particular the small diameters of 6 and 10 mm are perfect for the electronics industry and small parts assembly, where they simulate micro movements for testing control buttons, keyboards or similar.

Areas of application

- Linear short stroke movements.
- Pushing or pulling without any lateral loads.
- Primary tasks such as pushing of buttons and clamping of small parts.

The hallmarks of Festo products:

- Well designed
- Built-in reliability
- Easy to install
- Superb quality
- Quick delivery



Everyday products for everyday standard tasks. These products are designed to offer high functionality and compactness at the same high quality you expect from Festo for users looking for simple, cost-effective pneumatic control. This select range of products includes compact and robust valves, guided and mini slide units, compact cylinders, regulators, filter regulators and tubing. And they each form part of the Festo core product range - take advantage of products which offer shorter delivery times and competitive prices from one single source supplier.

Compact valve VUVG-S

24V DC

Get more power from a smaller design

Compact, inexpensive, high performance and installed in a flash. They're the perfect choice for all high-speed applications requiring a particularly high flow rate combined with a compact size. They offer essential features at an attractive price with the proven Festo quality.

Areas of application

- Designed for small to medium flow.
- Perfect for limited space requirements.
- Suitable for majority of applications including: electronics, food and end line packaging, textile, mobile applications, light assembly, conveyor systems.
- The lightweight aluminum housing is ideal for direct mounting on robot arms or cylinders.

High flow valve VUVS-S



The robust valve for harsh environments

High flow rate and elegant design. This series is a perfect example of heavy-duty pneumatics offering reliable operation at a great price. Combines features required for operation in harsh environments such as impact resistance, ease of installation, and mounting options, including manifolds.

Areas of application

- Single installations.
- Conveyor divertors and stops.
- Suitable for manifold mounting.
- Basic valves with focused features for 24V DC.
- Designed for medium to large flows.

Regulator and filter regulator MS2



Extremely lightweight and compact with high flow rates

Advanced polymer materials make the compressed air regulator and filter regulators up to 50% lighter than competitive products, but extremely sturdy at the same time. The optimized design provides a very high flow rate performance, while the stable control behavior ensures smooth processes. These strong, cost-efficient and lightweight components are ideal for use directly in the application and in the electronics industry.

Areas of application

- Minimal space requirements.
- Ideal for end-of-arm, small parts assembly and in the electronics industry.
- Designed for use close to the process directly in the machine.

Polyurethane tube PUN-H



Detect solid particles, moisture or oil in the line

PUN-H is the go-to-tube for a wide variety of applications including the exposure to wet environments, humidity and even outside thanks to its corrosion resistant properties. Combined with its high kink resistance, it's the ideal choice when selecting tubing for uninterrupted and reliable air supply. Thanks to its high quality base material, it is suitable for use both in the food industry and outdoors. Both transparent and non-transparent colors are available.

Areas of application

- General pneumatic automation.
- Used in the food zone.
- Environments with high moisture levels, weather resistant and resistance to UV radiation (black color).



Core Product Range

A star, a distinction, a promise: the best for your task. With the Festo core product range, you can choose from an extensive portfolio and benefit from high-quality components at particularly attractive prices.

Your first choice products for simple, cost-effective pneumatic control

Round cylinder DSNU-S



Round cylinders ideal for small spaces

When space is tight, the DSNU-S is the slimmest and shortest round cylinder for maximum space savings. The chosen materials and precision manufacturing provide durability and ensure reliable performance and longevity. Ideal for simple direct mounting and easy commissioning in combination with Festo's PPS cushioning, DSNU-S provides space-saving and tamper-proof performance in strokes up to 200mm.

Areas of application

- Linear, short to medium stroke movements.
- Pushing or pulling with minimal lateral loads.
- Ideal for use in tight spaces.

Round inch cylinder DPRA



Direct interchangeability with common inch round-body cylinders

The DPRA is Festo's direct interchange inch round-body pneumatic cylinder. Superior performance due to 303 stainless steel piston rod and 304 stainless housing providing corrosion resistance, low friction and long life. Oil-impregnated piston rod bushing and low friction U-cup seals create a pneumatic cylinder with efficient performance, superior service life and reliability. Premium lubrication provides excellent running characteristics and outstanding efficiency.

Areas of application

- Offers direct interchangeability within the product classification of non-repairable round-body cylinders.
- Optional high temperature and low temperature seals are available for special environments.
- An extensive range of variants and mounting accessories for most applications.

Everyday products for everyday standard tasks. These products are designed to offer high functionality and compactness at the same high quality you expect from Festo for users looking for simple, cost-effective pneumatic control. This select range of products includes compact and robust valves, guided and mini slide units, compact cylinders, regulators, filter regulators and tubing. And they each form part of the Festo core product range - take advantage of products which offer shorter delivery times and competitive prices from one single source supplier.

Compact inch cylinder DPCA



Fits to tight spaces, ideal for clamping and holding

Robust construction due to high quality, solid aluminum construction. The smooth, cylindrical body with protective clear anodized coating enables superior corrosion resistance. Premium lubrication provides excellent running characteristics and outstanding efficiency. Self-lubricating piston rod bearing and internally lubricated seals enables superior service life and reliability. Offers an extensive range of variants and mounting accessories for most applications.

Areas of application

- Self-lubricating piston rod bearing and internally lubricated seals enables superior service life and reliability.
- Available in a wide range of bore sizes from 1/2" to 4", and stroke lengths up to 4" as standard.
- Unique adjustable stroke version enables manual and precise stroke adjustment.
- An extensive range of variants and mounting accessories for most applications.

Compact inch cylinder DPCB



Superior reliability and service life

Superior performance due to high strength composite cylinder barrel with exceptional low friction and heat reducing operation.

Captive rod seals and rod bearing allow for hassle-free operation, and premium lubrication provides excellent running characteristics and outstanding efficiency.

Self-lubricating piston rod bushing and internally lubricated seals create a pneumatic cylinder with superior service life and reliability. The robust construction with clear anodized aluminum heads, stainless steel tie rods and hard chrome piston rods provide a durable cylinder for many applications.

Areas of application

- DPCB offers direct interchangeability within the product classification of compact pancake cylinders.
- Available in a wide range of bore sizes from 1/2" to 4", and stroke lengths, up to 4" as standard.
- An extensive range of variants and mounting accessories for most applications.
- CAD models for easier and faster design.

NFPA cylinder DSNA




The corrosion resistant and robust design make it an ideal choice

Repairable, pneumatic cylinder conforming to NFPA interchange dimensions. The cost-optimized design makes this an ideal choice for OEM machinery manufacturers. Sturdy construction with stainless steel tie-rods makes this cylinder highly suitable for industries like construction, agriculture, packaging and the automotive industry.

Areas of application


- Direct interchangeability with NFPA cylinders.
- Available in a range of bore sizes from 1.5" to 4".
- Corrosion resistant construction and special rod bushing make it suitable for harsh environments and high workload applications like stamping, construction and packaging.

Compact mini slide - DGST



Size [mm]	6	8	10	12	16	20	25
Stroke [mm]	Cushioning E1:	Elastic cushioning	g at both ends, no	end-position adj	ustment		
10	8078828 ★	8078833 🛨	8078839 ★	8078846 ★	8078853 🛨	8078862 ★	8078872 ★
20	8078829 ★	8078834 🛨	8078840 🛨	8078847 ★	8078854 ★	8078863 🛨	8078873 ★
30	8078830 🛨	8078835 ★	8078841 ★	8078848 🛨	8078855 🛨	8078864 ★	8078874 ★
40	8078831 ★	8078836 🛨	8078842 ★	8078849 ★	8078856 🛨	8078865 ★	8078875 ★
50	8078832 ★	8078837 ★	8078843 🛨	8078850 🛨	8078857 🛨	8078866 ★	8078876 🛨
80		8078838 ★	8078844 ★	8078851 🛨	8078858 🛨	8078867 ★	8078877 ★
100			8078845 ★	8078852 🛨	8078859 ★	8078868 ★	8078878 🛨
125					8078860 🛨	8078869 ★	8078879 ★
150					8078861 ★	8078870 ★	8078880 🛨
200						8078871 ★	8078881 ★
Stroke [mm]	Cushioning P: E	lastic cushioning	at both ends, non	-adjustable, with	end-position adj	ustment	
10	8085105	8085110	8085116	8085123	8085130	8085139	8085149
20	8085106	8085111	8085117	8085124	8085131	8085140	8085150
30	8085107	8085112	8085118	8085125	8085132	8085141	8085151
40	8085108	8085113	8085119	8085126	8085133	8085142	8085152
50	8085109	8085114	8085120	8085127	8085134	8085143	8085153
80		8085115	8085121	8085128	8085135	8085144	8085154
100			8085122	8085129	8085136	8085145	8085155
125					8085137	8085146	8085156
150					8085138	8085147	8085157
200						8085148	8085158
Stroke [mm]	Cushioning Y12	Shock absorbers	at both ends, sel	f-adjusting, with	end-position adju	ıstment	
30	8085159	8085162	8085166	8085171	8085176	8085183	8085191
40	8085160	8085163	8085167	8085172	8085177	8085184	8085192
50	8085161	8085164	8085168	8085173	8085178	8085185	8085193
80		8085165	8085169	8085174	8085179	8085186	8085194
100			8085170	8085175	8085180	8085187	8085195
125					8085181	8085188	8085196
150					8085182	8085189	8085197
200						8085190	8085198


Guided drive - DFM



Piston	6	10	12	16	20	25	32	40	50	63
Port	N	13		M5		G1/8			G1	L/ 4
Stroke [mm]	Plain-beari	ng guide GF -	high rigidity	thanks to la	rge-diameter	guide rods a	nd four plain	-bearing bus	hes	
5	4149944 ★	4154768 🛨								
10	4149945 🛨	4154769 🛨	170824 🛨	170832 🛨						
15	4149946 🛨	4154770 🛨								
20	4149947 🛨	4154799 🛨	170825 ★	170833 🛨	170840 ★	170847 ★	170854 🛨			
25			170826 🛨	170834 🛨	170841 ★	170848 🛨	170855 🛨	170864 🛨	170871 🛨	170878 🛨
30			170827 ★	170835 🛨	170842 ★	170849 ★	170856 🛨			
40			170828 🛨	170836 🛨	170843 🛨	170850 🛨	170857 🛨			
50			170829 🛨	170837 🛨	170844 🛨	170851 🛨	170858 🛨	170865 🛨	170872 🛨	170879 🛨
80			170830 🛨	170838 🛨	170845 ★	170852 🛨	170859 🛨	170866 🛨	170873 🛨	170880 🛨
100			170831 ★	170839 🛨	170846 ★	170853 🛨	170860 🛨	170867 🛨	170874 🛨	170881 🛨
125							170861 ★	170868 🛨	170875 🛨	170882 🛨
160							170862 ★	170869 🛨	170876 🛨	170883 🛨
200							170863 🛨	170870 🛨	170877 🛨	170884 🛨
Stroke [mm]	Recirculatin	ıg ball bearin	ng guide KF fo	or application	ns involving t	orque loads				
10			170899 🛨	170907 🛨						
20			170900 🛨	170908 🛨	170915 ★	170922 🛨	170929 🛨			
25			170901 🛨	170909 🛨	170916 🛨	170923 🛨	170930 🛨	170939 🛨	170946 🛨	170953 🛨
30			170902 🛨	170910 🛨	170917 🛨	170924 🛨	170931 🛨			
40			170903 🛨	170911 🛨	170918 🛨	170925 🛨	170932 🛨			
50			170904 🛨	170912 🛨	170919 🛨	170926 🛨	170933 🛨	170940 🛨	170947 🛨	170954 🛨
80			170905 🛨	170913 🛨	170920 🛨	170927 🛨	170934 🛨	170941 🛨	170948 🛨	170955 🛨
100			170906 🛨	170914 🛨	170921 🛨	170928 🛨	170935 🛨	170942 🛨	170949 ★	170956 🛨
125							170936 🛨	170943 🛨	170950 🛨	170957 🛨
160							170937 🛨	170944 ★	170951 🛨	170958 🛨
200							170938 🛨	170945 ★	170952 🛨	170959 🛨


Note: Piston sizes also available in 80 and 100mm bore. Please refer to the online catalog → www.festo.com/catalog/dfm

Compact cylinders - ADN-S/AEN-S



ston	Stroke [mm]	I - Piston rod with	female thread	A - Piston rod wi	th male thread				
DN-S [Double-a			a.c		R.C.				
	Without position sensing								
	5	4886885 🛨	ADN-S-6-5-I	8080598	ADN-S-6-5-A				
	10	4886886 🛨	ADN-S-6-10-I	8080596	ADN-S-6-10-A				
6mm	With position	sensing	·	-	ı				
	5	5173732 🛨	ADN-S-6-5-I-A	8080597	ADN-S-6-5-A-A				
	10	5173733 🛨	ADN-S-6-10-I-A	8080595	ADN-S-6-10-A-A				
	Without posi	tion sensing							
	5	4887523 🛨	ADN-S-10-5-I	8080589	ADN-S-10-5-A				
	10	4887524 🛨	ADN-S-10-10-I	8080588	ADN-S-10-10-A				
10mm	With position sensing								
	5	5177082 🛨	ADN-S-10-5-I-A	8080587	ADN-S-10-5-A-A				
	10	5177085 🛨	ADN-S-10-10-I-A	8080590	ADN-S-10-10-A-A				
N-S [Single-a	cting]								
	Without posi	tion sensing							
	5	4984929 🛨	AEN-S-6-5-I	8080593	AEN-S-6-5-A				
6mm	10	4984930 🛨	AEN-S-6-10-I	8080594	AEN-S-6-10-A				
OIIIII	With position sensing								
	5	5267300 🛨	AEN-S-6-5-I-A	8080591	AEN-S-6-5-A-A				
	10	5267301 🛨	AEN-S-6-10-I-A	8080592	AEN-S-6-10-A-A				
	Without posi	tion sensing							
	5	4891759 🛨	AEN-S-10-5-I	8080583	AEN-S-10-5-A				
40	10	4891760 🛨	AEN-S-10-10-I	8080586	AEN-S-10-10-A				
10mm	With position	sensing							
	5	5269268 🛨	AEN-S-10-5-I-A	8080584	AEN-S-10-5-A-A				
	10	5269269 🛨	AEN-S-10-10-I-A	8080585	AEN-S-10-10-A-A				

Compact valves - VUVG-LK/BK [24V DC]



In-line valve	s - LK					
Connection size	Width [mm]	Part No	Description	Part No	Description	Flow rate
With electri	ical sub-b	ase R8 [3-pin]		With electrica	al sub-base H2 [2-pin]	
2 x 3/2-way	y with sol	enoid coil, norn	nally closed, pneumatic spring 24\	' DC		
M5	10	8042542 🛨	VUVG-LK10-T32C-AT-M5-1R8L-S	8042538 🛨	VUVG-LK10-T32C-AT-M5-1H2L-S	180 l/min
M7	10	8042550 🛨	VUVG-LK10-T32C-AT-M7-1R8L-S	8042546 ★	VUVG-LK10-T32C-AT-M7-1H2L-S	280 l/min
G1/8	14	8042566 🛨	VUVG-LK14-T32C-AT-G18-1R8L-S	8042562 🛨	VUVG-LK14-T32C-AT-G18-1H2L-S	570 l/min
5/2-way wi	th soleno	oid coil single so	olenoid 24V DC			
M5	10	8042543 🛨	VUVG-LK10-M52-AT-M5-1R8L-S	8042539 🛨	VUVG-LK10-M52-AT-M5-1H2L-S	195 l/min
M7	10	8042551 🛨	VUVG-LK10-M52-AT-M7-1R8L-S	8042547 ★	VUVG-LK10-M52-AT-M7-1H2L-S	340 l/min
G1/8	14	8042567 🛨	VUVG-LK14-M52-AT-G18-1R8L-S	8042563 🛨	VUVG-LK14-M52-AT-G18-1H2L-S	660 l/min
5/2-way wi	th soleno	oid coil double s	solenoid 24V DC			
M5	10	8042544 🛨	VUVG-LK10-B52-T-M5-1R8L-S	8042540 ★	VUVG-LK10-B52-T-M5-1H2L-S	195 l/min
M7	10	8042552 🛨	VUVG-LK10-B52-T-M7-1R8L-S	8042548 🛨	VUVG-LK10-B52-T-M7-1H2L-S	340 l/min
G1/8	14	8042568 🛨	VUVG-LK14-B52-T-G18-1R8L-S	8042564 🛨	VUVG-LK14-B52-T-G18-1H2L-S	660 l/min

Sub-base valves - BK (connection via supply manifold)


Connection size	Width [mm]	Part No	Description	Part No	Description	Flow rate	
With electrical sub-base R8 [3-pin] With electrical sub-base H2 [2-pin]							
2 x 3/2-way	with sole	noid coil, norma	ally closed, pneumatic spring 24V D	C			
M5/M7	10	8042558 🛨	VUVG-BK10-T32C-AT-F-1R8L-S	8042554 🛨	VUVG-BK10-T32C-AT-F-1H2L-S	160 l/min	
G1/8	14	8042574 🛨	VUVG-BK14-T32C-AT-F-1R8L-S	8042570 🛨	VUVG-BK14-T32C-AT-F-1H2L-S	350 l/min	
5/2-way wit	h solenoi	d coil single sol	enoid 24V DC				
M5/M7	10	8042559 🛨	VUVG-BK10-M52-AT-F-1R8L-S	8042555 🛨	VUVG-BK10-M52-AT-F-1H2L-S	160 l/min	
G1/8	14	8042575 🛨	VUVG-BK14-M52-AT-F-1R8L-S	8042571 ★	VUVG-BK14-M52-AT-F-1H2L-S	380 l/min	
5/2-way with solenoid coil double solenoid 24V DC							
M5/M7	10	8042560 🛨	VUVG-BK10-B52-T-F-1R8L-S	8042556 🛨	VUVG-BK10-B52-T-F-1H2L-S	160 l/min	
G1/8	14	8042576 ★	VUVG-BK14-B52-T-F-1R8L-S	8042572 ★	VUVG-BK14-B52-T-F-1H2L-S	380 l/min	

Elect	Electrical connections					
H2	2	Plug socket with cable, 2.5 m length	566656 🛨	NEBV-H1G2-KN-2.5-N-LE2		
R8	3	M8 cable, 3-pin open end, 2.5 m length	541338 🛨	NEBU-M8W3-K-2.5-LE3		

Accessories:

Manifold options including pre-assembled with valves via 572230 VTUG-S

High flow valves - VUVS-LK [24V DC]




In-line valves - LK

Connection size	G1/8	G1/4	G3/8
Valve width [mm]	20	25	30
Flow rate l/min	550	1,000	1,600
Temperature range [°C]		-5 +50	
Operating voltage		24V DC	
3/2-way valve	8043213 ★	8043217 ★	8049880 ★
	VUVS-LK20-M32C-AD-G18-1C1-S	VUVS-LK25-M52-AD-G14-1B2-S	VUVS-LK30-M32C-AD-G38-1B2-S
5/2-way valve	8043214 ★	8043218 ★	8049881 ★
single solenoid	VUVS-LK20-M52-AD-G18-1C1-S	VUVS-LK25-M52-AD-G14-1B2-S	VUVS-LK30-M52-AD-G38-1B2-S
5/2-way valve	8043215 ★	8043219 ★	8049882 ★
double solenoid	VUVS-LK20-B52-D-G18-1C1-S	VUVS-LK25-B52-D-G14-1B2-S	VUVS-LK30-B52-D-G38-1B2-S
Plug socket	151687 ★	34431 ★	34431 ★
	MSSD-EB	MSSD-F	MSSD-F
Plug socket with cable 2.5m length	151688 ★	30935 ★	30935 ★
	KMEB-1-24-2,5-LED	KMF-1-24DC-2,5-LED	KMF-1-24DC-2,5-LED
Plug socket with cable	151689 ★	30937	30937
5m length	KMEB-1-24-5-LED	KMF-1-24DC-5-LED	KMF-1-24DC-5-LED

Manifold - Compact mani	fold block VABM with gaskets and so	crews included	
3/2 - 2 position	576465 ★ 576467 ★	8026297 ★	8026413 ★
3/2 - 4 position	576467 🛨	8026299 ★	8026415 ★
3/2 - 6 position	576469 🛨	8026301 ★	8026417 ★
3/2 - 8 position	576471 ★	8026303 🛨	8026419 ★
3/2 - 10 position	576473 ★	8026305 ★	8026421 ★
5/2 - 2 position	576417 🛨	8026261 ★	8026377 ★
5/2 - 4 position	576419 🛨	8026263 🛨	8026379 ★
5/2 - 6 position	576421 🛨	8026265 ★	8026381 ★
5/2 - 8 position	576423 ★	8026267 ★	8026383 ★
5/2 - 10 position	576425 🛨	8026269 ★	8026385 ★
Screw set	8069876 🛨	8068789 ★	8068790 🛨

Regulators/Filter regulators - MS2-LR/LFR



Regulator						
Product Image	Туре	Size	Part No	Description	Flow rate	Weight
	Pressure reg	ulation range 0.5	7 bar, rotary kn	ob with detent [Bar/psi]		
	MS2-LR	M5	8086628 🛨	MS2-LR-M5-D6-AR-BAR-B	170 l/min	39.8 g
	MS2-LR	QS-6	8086638 🛨	MS2-LR-QS6-D6-AR-BAR-B	350 l/min	36.6 g
	With pressure gauge, display unit [MPa]					
6-16	MS2-LR	M5	8086636	MS2-LR-M5-D6-AR-MPA-B	170 l/min	39.8 g
	MS2-LR	QS-6	8086639	MS2-LR-QS6-D6-AR-MPA-B	350 l/min	36.6 g
	With adapter	for EN pressure	gauge 1/8, withou	t pressure gauge		
	MS2-LR	M5	8086637 ★	MS2-LR-M5-D6-A8-B	250 l/min	34.8 g
	MS2-LR	QS-6	8086640 🛨	MS2-LR-QS6-D6-A8-B	350 l/min	31.6 g

Filter Regulator								
Product Image	Туре	Size	Part No	Description	Flow rate	Weight		
Contract of the Contract of th	Pressure regul	ation range 0.5	7 bar, rotary	knob with detent with manual conde	ensate drain, 5µm	[Bar/psi]		
	MS2-LFR	M5	8086641 ★	MS2-LFR-M5-D6-AR-BAR-C-M-B	140 l/min	47.3 g		
	MS2-LFR	QS-6	8086644 ★	MS2-LFR-QS6-D6-AR-BAR-C-M-B	310 l/min	45 g		
	With pressure	gauge, display	unit [MPa]					
	MS2-LFR	M5	8086642	MS2-LFR-M5-D6-AR-MPA-C-M-B	140 l/min	47.3 g		
	MS2-LFR	QS-6	8086645	MS2-LFR-QS6-D6-AR-MPA-C-M-B	310 l/min	45 g		
	With adapter for EN pressure gauge 1/8, without pressure gauge							
	MS2-LFR	M5	8086643 ★	MS2-LFR-M5-D6-A8-C-M-B	140 l/min	42.3 g		
	MS2-LFR	QS-6	8086646 🛨	MS2-LFR-QS6-D6-A8-C-M-B	310 l/min	40 g		

Accessories						
Туре	Part No	Description				
Filter cartridge 5µm	526818	LFP-D-MICRO-5M				
Wall bracket	8087978 🛨	MS2-WR				
Knurled nut	8098037 🛨	MS2-WRS				



Polyurethane tubing - PUN-H



- Sizes 2mm OD up to 16mm OD
- Highly flexible tubing
- Resistant to hydrolysis and microbes
- UV-resistant
- Food-safe
- FDA-listed material
- Kink-resistant
- Red, green and yellow tube also available
- DUO tube available in Blue & Black

PUN-H - Vers	satile range of	solid colors	_					
OD	Packed length	Packaging Material	Blue	Black	Silver	Red	Green	Yellow
2mm	50m	Вох		133039		133040		
3mm	50m	Вох	197382	197389	558277	558284	558291	558298
וווווו	500m	Spool	558256	558249	558270			
li ma ma	50m	Вох	197383 🛨	197390 🛨	558278 🛨	558285	558292	558299
4mm	500m	Spool	558257	558250 💢	558271 🏠			
C	50m	Box	197384 🛨	197391 ★	558279 ★	558286	558293	558300
6mm	500m	Spool	558258	558251 🏠	558272			
0	50m	Box	197385 🛨	197392 ★	558280 ★	558287	558294	558301
8mm	400m	Spool	558259	558252	558273			
10mm	50m	Box	197386 🛨	197393 🛨	558281 ★	558288	558295	558302
	300m	Spool	558260	558253	558274			
12	50m	Вох	197387 🛨	197394 ★	558282 ★	558289	558296	558303
12mm	200m	Spool	558261	558254	558275			
14mm	50m	Box	570386	570387				
4.6	50m	Box	197388	197395	558283	558290	558297	558304
16mm	100m	Spool	558262	558255	558276			
1/8 in	150ft	Box	567945 🛨	567953 🛨	567937 ★		567977	
5/32 in	150ft	Box	567946 🛨	567954**				
3/16 in	150ft	Box	567947	567955			567979	567971
1/4 in	150ft	Box	567948**	567956**	567940**	567988	567980	567972
5/16 in	150ft	Box	567949 🛨	567957 🛨				
3/8 in	150ft	Box	567950**	567958**	567942 🛨	567990	567982	567974
1/2 in	150ft	Box	567951 🛨	567959 🛨	567943 🛨	567991	567983	567975
5/8 in	150ft	Box	567952	568008		567992	567984	567976

^{*}Also available in bulk quantities on reels.

NOTE: Additional materials, sizes and colors are also available. Please contact Festo.

Ready for dispatch from the Festo factory in 24 hours

Ready for dispatch from the Festo factory in 5 days

Polyurethane tubing - PUN-H




Spool Box

OD	Packed length	Packaging Material	Natural (Clear)	Translucent blue	Translucent black	Translucent red	Translucent green	Translucent yellow
2mm	50m	Box	133038					
2 mm	50m	Box	197375					
3mm	500m	Spool	558263					
/1 ma ma	50m	Box	197376 🛨	8048671 🛨	8048673 🛨	8048675	8048677	8048679
4mm	500m	Spool	558264	8048672 太	8048674			
(50m	Box	197377 🛨	8048681 ★	8048683 🛨	8048685	8048687	8048689
6mm	500m	Spool	558265 🏠	8048682 太	8048684			
0	50m	Box	197378 🛨	8048691 ★	8048693 🛨	8048695	8048697	8048699
8mm	400m	Spool	558266	8048692	8048694			
10	50m	Box	197379 🛨	8048701 🛨	8048703 🛨	8048705	8048707	8048709
10mm	300m	Spool	558267	8048702 🏠	8048704			
12mm	50m	Box	197380 🛨	8048711 🛨	8048713 🛨	8048715	8048717	8048719
12111111	200m	Spool	558268	8048712	8048714			
14mm	50m	Box	570388					
16	50m	Box	197381					
16mm	100m	Spool	558269					
1/8 in	150ft	Box	567961 ★					
5/32 in	150ft	Box						
3/16 in	150ft	Box	567963					
1/4 in	150ft	Box	567964**	13121063 🛨				
5/16 in	150ft	Box	567965**					
3/8 in	150ft	Box	567966**	13121062 🛨				
1/2 in	150ft	Box	567967 🛨	13124064 🛨				
5/8 in	150ft	Box						

^{*}Also available in bulk quantities on reels.


NOTE: Additional materials, sizes and colors are also available. Please contact Festo.

Round cylinder - DSNU-S



Piston	8	12	16	20	25	16	20	25
	Cushioning - P	Position sensi	ng - A			Cushioning - P	PS Position ser	nsing - A
Stroke [mm]								
10	5205897 ★	5211896 🛨	5216087 ★	5224633 ★	5228227 ★			
15	5205898 🛨	5211897 ★	5216088 🛨	5224634 🛨	5228228 🛨			
20	5205899 🛨	5211898 🛨	5216089 🛨	5224635 🛨	5228229 ★			
25	5205900 🛨	5211899 🛨	5216090 🛨	5224637 🛨	5228230 🛨	5217238 🛨	5225836 🛨	5228452 🛨
30	5205902 🛨	5211900 🛨	5216091 ★	5224639 ★	5228231 ★	5217239 ★	5225837 ★	5228453 🛨
40	5205903 🛨	5211901 🛨	5216093 🛨	5224641 ★	5228232 🛨	5217240 🛨	5225838 🛨	5228454 ★
50	5205904 ★	5211903 🛨	5216094 🛨	5224642 🛨	5228233 ★	5217241 ★	5225839 🛨	5228455 ★
60	5205905 🛨	5211904 🛨	5216095 🛨	5224643 ★	5228234 ★	5217242 ★	5225840 ★	5228456 🛨
80	5205906 🛨	5211905 🛨	5216096 🛨	5224644 ★	5228235 ★	5217243 ★	5225841 ★	5228457 ★
100	5205907 ★	5211906 🛨	5216098 🛨	5224645 ★	5228236 ★	5217244 ★	5225842 ★	5228458 🛨
125		5211908 🛨	5216099 🛨	5224645 ★	5228237 🛨	5217245 ★	5225843 ★	5228459 ★
150		5211909 ★	5216100 🛨	5224646 ★	5228238 🛨	5217246 ★	5225844 ★	5228460 🛨
200			5216101 🛨	5224647 🛨	5228239 🛨	5217248 🛨	5225846 🛨	5228461 ★

Interchangeable inch round air cylinder - DPRA



Piston diameter [in]	3/4	1 1/16	1 1/4	11/2	13/4	2	2 1/2	Code						
Part No.	8109549	8109550	8109551	8109552	8109553	8109554	8109555							
Function	Round cylinde	er						DPRA						
Stroke	0.0625 12").0625 12 "												
Function	Double-acting	Double-acting												
	At one end													
Piston rod type	Through pisto	on rod			-	Through piston rod	-	Т						
Compressed air	Lateral													
supply port	Axial													
Cuchioning	No cushioning													
Cushioning	Flexible cushioning rings/pads at both ends													
Docition consinu	Without													
Position sensing	For proximity switch													
Town overture were	Standard													
Temperature range	+32 +300 °F													
Piston rod	Without													
extension	0 6 inch													
Piston rod thread	Without													
extension	0 6 inch													

Choice of mounting styles:

- Mounting thread
- Rear swivel
- Trunnion flange
- Block mount

Solid aluminum inch compact cylinder - DPCA



Piston diameter [in]	1/2	3/4	1 1/8	1 5/8	2	2 1/2	3	4	Code		
Part No.	8104871	8104872	8104873	8104874	8104875	8104876	8104877	8104878			
Function	Compact cylin	nder	,						DPCA		
System of											
units											
Anti-twist	Without										
protection	-	With anti-twis	st protection						-Q		
Running	Standard										
characteris- tics	Additional PTFE piston guide										
Stroke	Up to 4"										
Stroke	Without										
adjustment	-	-	Advancing/fr	ont							
	At one end										
Piston rod type	Through, hollow piston rod										
.,,,,	Through pisto	on rod							T		
Piston rod	External threa	ad									
thread type	Internal threa	nd							F		
Position	Without										
sensing	For proximity	switch							Α		
Scraper	None										
variant	Increased che	emical resistan	ce						-A1		

Additional options:

- Mounting (swivel clevis, rod eye)
- Cushioning (bumpers)

Interchangeable inch compact cylinder - DPCB




Piston diameter [in]	1/2	3/4	1 1/16	1 1/2	2	2 1/2	3	4	Code			
Part No.	8104879	8104880	8104881	8104882	8104883	8104884	8104885	8104886				
Function	Compact cylir	nder							DPCB			
Anti-twist	Without											
protection	- With double piston rod											
Running	Standard											
characteris- tics	Low friction	ow friction										
Stroke	Up to 4"											
D	At one end	At one end										
Piston rod type	Through, hollow piston rod											
3,70	Through pisto	Through piston rod										
	One end plate	e										
Piston rod	One end plate with recess and through-hole											
design	One end plate, rotated 90°											
	One end plate with recess and through-hole, rotated 90°											
Piston rod	External threa	ad										
thread type	Internal threa	ad							F			
	No thread								N			
Position	Without											
sensing	For proximity	switch							Α			
Temperature									-T3			
range	40 +176°F											
Scraper	None											
variant	Increased chemical resistance											
	Scraper made of NBR											

Additional options:

- Mounting (threads, through holes, swivel, trunnion)
- Cushioning (bumpers)

NFPA interchange cylinder - DSNA



Piston diameter [in]	1 1/2	2	2 1/2	3 1/4	4	Code				
Part No.	8117043	8117044	8117045	8117046	8117047					
Function	Standards-base	Standards-based cylinder, double-acting								
System of units	Imperial	Imperial								
Stroke	0.25 48"	0.25 48"								
Dieten ved ture	At one end									
Piston rod type	Through piston rod									
Cushioning	Pneumatic cush	Pneumatic cushioning, adjustable at both ends								
Position sensing	For proximity switch									
Standard	Conforms to ANSI/NFPA									
	Flange plate, bearing cap									
	Flange plate, end cap									
Type of mounting	Swivel bearing									
Type of illounting	Swivel mounting									
	Foot mounting									
	Direct mounting									
	Detachable eye mount									
	Mid trunnion									
Cool material	Extended tie rods, rear									
Seal material	Extended tie rods, front									
	Standard									
	Viton					-T2				

Online services and support tools provide online assistance

You can find all the important services and tools online at any time, from helpful video tutorials to comprehensive information about our products and software. They are available to you whenever you need them and wherever you are. All the information can be accessed 24 hours a day.



Online engineering services

The quick and easy way to your goal. The productivity circle will always point you to the right services and software tools from Festo. From the Product Finder and configuration to CAD downloads, you will find lots of tools that make your work quicker and easier. So you have a virtual method to design your systems, whenever and wherever you are.





All the product information at your fingertips

In the Support Portal you will find all the important information: documentation on commissioning, information about spare parts, instructions manuals and much more.


→ To the Support Portal



Video tutorials: watch and apply straight away

Our YouTube channel "Festo Service" shows you how you can configure, repair, commission and adapt Festo products. Our tutorials are a perfect complement to our technical hotline. They will show you around the clock how you can carry out work on components correctly and directly.

→ To our YouTube channel



QuickSearch plus tool

When you know the part number or description of the parts you need this is the fastest way to access all the information you need including: CAD files, EPLAN data, product accessories, operating instructions, spare parts.

→ Download now




Convenient purchasing in the Online Shop

In our Online Shop you will find 35,000 components including electric drives, pneumatic automation, control technology, software and valve terminals. And of course you can order around the clock.

→ To the Online Shop

Festo - Your Partner in Automation





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

Festo Customer Interaction Center

Tel: 1877 463 3786 Fax: 1877 393 3786

Email: customer.service.ca@festo.com | ventas.mexico@festo.com



Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

Multinational Contact Center

01 800 337 8669



Festo Corporation

1377 Motor Parkway Suite 310 Islandia, NY 11749



Regional Service Center

7777 Columbia Road Mason, OH 45040

Festo Customer Interaction Center

1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Connect with us







