



GENERAL TOLERANCE					
DIM. RANGE	≤ 3	> 3 ~ 6	> 6 ~ 30	> 30 ~ 120	> 120 ~ 400
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5

ORIGINAL COPY(正宗原版)
1 8 OCT 2023
DOCUMENT CONTROL



Handshake PV-693781-000



REVISIONS		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	2023-10-18

4. THE CRIMPING COMPRESSION RATIO WITHIN 70%-90% WITH UL 12&10&8AWG CABLE.
3. THE HANDSHAKE MOVING MECHANISM IS ALLOWED TO HAVE LUBRICATING OIL, BUT CANNOT OVERFLOW. OTHER PART SURFACE SHOULD BE CLEAN AND WITHOUT OIL OR OXIDATION.
2. SPECIFIED GENERAL TOLERANCE
- A. ALL THE ROUNDED CORNERS RADIUS 0.3mm MIN.
 - B. BURRS NOT TO EXCEED 0.03mm FOR ANY SURFACE.
1. THE REFERENCED MATERIAL SHALL BE CERTIFIED COMPLIANT TO THE LATEST ROHS AND REACH REQUIREMENT.
- NOTES:

Crimping die PV-693782-005

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS	POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN: MILLIMETERS TOLERANCES: ANGLES= ±2° DEFAULT LINEAR TOLERANCES SEE TABLE DIM & TOL. PER ASME Y14.5M-1994; DRM PER MIL-DTL-31000; OTHER AMPHENOL STANDARDS: 9-9318	MATERIAL SPEC.	APPROVALS		DATE	PARTS LIST	
	N/A	APPROVED BY PETER XIA		2023-10-18	Amphenol Technology (ShenZhen) Co., Ltd. Building C, Xia Shi Jia 2nd Industrial Estate, Gongming, Shenzhen, 518106, China.	
		CHECKED BY			Crimping tool for 4/6/10mm2 S&F contact	
		DESIGN MANAGER				
		DESIGN AUTHORITY GROUP				
	PROCESS SPEC.	THIRD ANGLE PROJECTION			DOCUMENT NO.	REV.
N/A				PV-693780-004	A	
				SCALE: 1:0	SHEET 1 OF 1	