

VB: 50 mm, 3W, Globe, FLG, BR, 38 kvs, Glycol 25-50% and Water, Venta, No Steam

7311145000

EAN Code: 3606489658670

Main

····a···		
Valve product range	Venta	
Product or component type	Valve	
Valve type	Globe	
Valve product series	V311	
Valve model	V311/50/38	
Medium compatibility	Glycol 25 % Water Glycol 30 % Glycol 50 %	
Valve configuration	3-Way	
Valve connection type	Flanged	
Valve connection size	DN50 (ISO 7005-2)	
Body size	50 mm (2 in)	
Pipe size	50 mm	
Flow characteristic	Equal percentage	
Flow coefficient	43.94 cv 38 kvs	
Pressure class	PN16	
Operating fluid temperature	-20120 °C	
Pressure fluid max delta P normal life	I 399.9 kPa	
Control valve rangeability	Greater than 50:1	
Stroke length	20 mm	
Seat leakage	Port A: Class IV-S1 (0.005 %)	
Stem flow action	Stem up closes A and opens B to AB	
Stem movement	Linear	
Trim material	Brass	
Body material	Nodular cast iron EN-JS 1030	
Seat material	Port A: nodular cast iron EN-JS 1030 Port B: nodular cast iron EN-JS 1030	
Stem material	Stainless steel AISI 303	
Plug material	CW602N brass	
Stem seal material	EPDM (ethylene propylene diene monomer)	
Seating seal material	Port A:EPDM (ethylene propylene diene monomer) Port B:EPDM (ethylene propylene diene monomer)	

Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific.
	Australia.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	23.5 cm
Package 1 Length	28.5 cm
Package 1 Weight	10.35 kg

Logistical informations

Country of origin S

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

∅ Environmental fellow	ootprint
------------------------	----------

Environmental Disclosure Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No