

Voltage release, TeSys GV4, MX coil, 380 to 415VAC 50Hz, 440 to 480VAC 60Hz

GV4AS487

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range | TeSys | |
|------------------------------|--|--|
| Device short name | MX | |
| Product or Component Type | Voltage release | |
| Device Application | Control | |
| Range compatibility | TeSys TeSys GV4 TeSys TeSys BV4 | |
| Voltage release type | Shunt trip release | |
| [Uc] control circuit voltage | 440480 V AC 60 Hz 380. 415 V AC 50 Hz | |

Complementary

| • | | |
|---|---|--|
| [Ui] rated insulation voltage | 480 V IEC 60947-1 | |
| Threshold tripping voltage | 0.71.1 Un failsafe opening < 0.7 Un possible opening | |
| Impulse duration | >= 20 ms | |
| Mounting Mode | Internal mounting | |
| Maximum inrush power in VA | 6 VA | |
| Maximum hold-in power consumption in VA | 10 VA | |
| Mechanical durability | 20000 cycles | |
| Operating time | < 50 ms | |
| Connections - terminals | Spring terminals 1 0.00080.002 in² (0.51.5 mm²) - cable stiffness: flexible without cable end | |
| Wire stripping length | 0.3 in (8 mm) | |

Environment

Quantity per Set Set of 1

Ordering and shipping details

| Category | US10I1122366 |
|-------------------|---------------|
| Discount Schedule | 0111 |
| GTIN | 3606485444925 |
| Returnability | No |
| Country of origin | FR |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

| 11.81 in (30.0 cm) | |
|--------------------|--|
| | |
| | |
| | |
| | |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∅ Environmental footprint | | |
|--|-------------------------------|--|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 2 | |
| Environmental Disclosure | Product Environmental Profile | |

Use Better

| Materials and Substances | |
|--|---|
| Recycled metal content at CR level | 0 |
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Compliant with Exemptions |
| SCIP Number | 75582d60-9779-4641-a03b-18e996230a58 |
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| Halogen content performance | Product contains halogen above thresholds |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|--|
| Circularity Profile | End of Life Information |
| Take-back | No |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |