

FBSK 10-10 - Plug-in bridge

1928437

<https://www.phoenixcontact.com/gb/products/1928437>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bridge, fully insulated, pitch 10 mm, 10-pos.

Commercial data

Item number	1928437
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AARZFE
Product key	AARZFE
Catalog page	Page 830 (C-1-2013)
GTIN	4017918613792
Weight per piece (including packing)	11.41 g
Weight per piece (excluding packing)	11.396 g
Customs tariff number	85389099
Country of origin	PL

FBSK 10-10 - Plug-in bridge

1928437

<https://www.phoenixcontact.com/gb/products/1928437>



Technical data

Product properties

Product type	Bridge
Product family	FBSK
Product line	COMBICON Terminals Special
Number of positions	10
Pitch	10 mm
Number of connections	10
Number of rows	1
Number of potentials	10

Dimensions

Pitch	10 mm
-------	-------

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy

Material data - housing

Color (Housing)	red (3001)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

Connector

Connection 1

Insulating material	PA
CTI according to IEC 60112	600

FBSK 10-10 - Plug-in bridge

1928437

<https://www.phoenixcontact.com/gb/products/1928437>



Classifications

ECLASS

ECLASS-13.0	27460406
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBSK 10-10 - Plug-in bridge

1928437

<https://www.phoenixcontact.com/gb/products/1928437>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.143 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk