



## Technical data

### KR80XLLH/3AS

Cam follower with shaft

#### PRODUCT DEFINITION

|                                                              |         |
|--------------------------------------------------------------|---------|
| <b>Brand</b>                                                 | NTN     |
| <b>D - External diameter</b>                                 | 80 mm   |
| <b>d1 - Stud diameter</b>                                    | 30 mm   |
| <b>C - Width of bearing, drawn cup or outer ring</b>         | 35 mm   |
| <b>F - Under roller diameter</b>                             | 38 mm   |
| <b>B - Bearing/Inner ring width</b>                          | 37 mm   |
| <b>B1 - Total stud length</b>                                | 100 mm  |
| <b>B2 - Stud rod length</b>                                  | 63 mm   |
| <b>G - Stud thread designation</b>                           | M30X1.5 |
| <b>G1 - Thread length of the stud</b>                        | 32 mm   |
| <b>B3 - Distance between washer face and radial lub hole</b> | 15 mm   |
| <b>C1 - Distance between roller face and washer face</b>     | 1 mm    |
| <b>n - Axial lubrication hole diameter</b>                   | 8 mm    |
| <b>a - Radial lubrication hole diameter</b>                  | 4 mm    |
| <b>e - Inlet diameter of roller or washer</b>                | 53 mm   |
| <b>h - Hexagonal hole</b>                                    | 8 mm    |
| <b>Maximum tightening torque</b>                             | 360 N-m |
| <b>Bearing with/without cage</b>                             | Avec    |
| <b>Radial clearance class</b>                                | CN      |



#### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## PRODUCT DEFINITION

|                        |         |
|------------------------|---------|
| <b>Precision class</b> | P0      |
| <b>Mass</b>            | 1,55 kg |

## PRODUCT PERFORMANCE

|                                                   |             |
|---------------------------------------------------|-------------|
| <b>Cr - Dynamic load rating</b>                   | 45000000 mN |
| <b>C0r - Static load rating</b>                   | 88500000 mN |
| <b>Track load capacity cylindrical outer ring</b> | 53000000 mN |
| <b>N lim - Grease lubrication limit speed</b>     | 24000 °/s   |
| <b>Tmin - Min operating temperature</b>           | 253,15 °K   |
| <b>Tmax - Max operating temperature</b>           | 373,15 °K   |

