




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A		2023.12.19	Initial Release	Yours

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal Body: PA66,
- Item ② Terminal lever: PBT ,
- Item ③ Terminal Cover: PA66 ,
- Item ④ Spring: Stainless
- Item ⑤ Terminal Contact: Copper alloy,

Electrical:	UL1059	Group B/G	Group C	Group D	Group F
●Voltage rating:	300 V		150 V	300V	400V
●Current rating:	16A		16A	16A	16A
●Wire range:					
Solid wire:	24-12AWG				
Stranded wire:	24-12AWG				
●Wire strip length:	11-13 mm				
●Withstanding Voltage:	1.6KV AC				
●Insulation Resisance:	DV500V 500MΩ min				
●Operating temperature:	-20℃ to +105℃				
●Assembling temperature:	-5℃ to +105℃				
●Safety Approval:	cULus				

Part No. QT xx B SB x x H xxxx G

NO. OF POLES
02: 2 POLES
03: 3 POLES
...
16: 16 POLES

Body color
0: Black
1: Natural color
2: Red
3: Orange
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey (標準色)
9: White
C: Green
(RAL 6018/U)

Lever color
0: Black
1: Natural color
2: Red
3: Orange (標準色)
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey
9: White
C: Green
(RAL 6018/U)

RoHS compliant
(lead<4%)
In copper Alloy
00x0: "@" Logo (Standard)
00xA: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	QT series pitch 7.5mm PCB terminal block,									
PART NO.	QTxxBSBxxHxxxxG				DWG NO.	8QT0102				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance	
Roy 2024.11.07	Roy 2024.11.07	Yours 2023.12.19	Yours 2023.12.19		UNIT: mm				X.	±0.50
					SCALE: 2:1				X.X	±0.30
					REV.: A0				X.XX	±0.10
				SHEET: 01/01					X°	±1°