



**Part Number :** [151360401](#)

**Product Description :** MicroClasp-to-MicroClasp  
Off-the-Shelf (OTS) Cable Assembly, Single Row,  
100.00mm Length, 4 Circuits, White

**Series Number :** 15136

**Status :** Active

**Product Category :** Power and Signal Cable  
Assemblies



---

## Documents & Resources

### Drawings

[151360401\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	15136
Description	MicroClasp-to-MicroClasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 100.00mm Length, 4 Circuits, White
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp-to-MicroClasp
Product Name	MicroClasp
Type	Discrete Wire Assembly
UPC	191128149792

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

### Physical

Cable Length	100.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	White
Gender	Female-Female

Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	2.744/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	22

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MicroClasp Vertical Single Row Headers	<u>55932</u>
MicroClasp Right-Angle Single Row Headers	<u>55935</u>