



FAG

NJ2320-E-XL-M1-C3




Cylindrical roller bearing

Cylindrical roller bearing NJ...-E-XL-M1, with cage, single row, semi-locating bearing, 2 ribs on outer ring, 1 rib on inner ring, type NJ

Schaeffler ID:
0192263300030

X-life

Technical information




Your current product variant

Design	E	Increased Capacity Design
Cage	M1	Two Piece Brass Cage Roller Guided
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Tolerance class	PN	Normal (PN)
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	215 mm	Outside diameter
B	73 mm	Width
C _r	680.000 N	Basic dynamic load rating, radial
C _{0r}	720.000 N	Basic static load rating, radial
C _{ur}	125.000 N	Fatigue load limit, radial
n _G	5.600 1/min	Limiting speed
n _{gr}	2.500 1/min	Reference speed
≈m	12,94 kg	Weight



Mounting dimensions

$d_{a \min}$	114 mm	Minimum diameter shaft shoulder
$d_{a \max}$	125 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	201 mm	Maximum diameter of housing shoulder
$d_{c \min}$	143 mm	Minimum shaft shoulder

$r_{a \max}$ 2,5 mm Maximum recess radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
$r_{1 \min}$	3 mm	Minimum chamfer dimension
s	4,2 mm	Axial displacement
E	191,5 mm	Raceway diameter outer ring
F	127,5 mm	Raceway diameter inner ring
$D_{1 \min}$	181,95 mm	Minimum rib diameter outer ring
d_1	139,4 mm	Maximum rib diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Additional information

HJ2320-E L-washer

Characteristics

-  F_r Radial load
-  F_a Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed