






LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECR-10-025509	15DEC2010	HMR	DD



2 POSITION
SHOWN AS SHIPPED



2 POSITION
SHOWN CLOSED
SCALE 8:1



RED	17.70	24 AWG	4	3-2106489-4
	13.70	24 AWG	3	3-2106489-3
	9.70	24 AWG	2	3-2106489-2
	5.70	24 AWG	1	 3-2106489-1
GREEN	17.70	22 AWG	4	2-2106489-4
	13.70	22 AWG	3	2-2106489-3
	9.70	22 AWG	2	2-2106489-2
	5.70	22 AWG	1	 2-2106489-1
BLUE	17.70	20 AWG	4	1-2106489-4
	13.70	20 AWG	3	1-2106489-3
	9.70	20 AWG	2	1-2106489-2
	5.70	20 AWG	1	 1-2106489-1
YELLOW	17.70	18 AWG	4	2106489-4
	13.70	18 AWG	3	2106489-3
	9.70	18 AWG	2	2106489-2
	5.70	18 AWG	1	 2106489-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

- ① MATERIALS AND FINISH: TYP

 - HOUSING: LCP, COLOR: NATURAL
 - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

3. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

4. 18AWG SOLID OR STRANDED WIRE, PRE-BONDED, 19 STRANDS OR LESS:

 - 18 AWG MAX INSULATION OD: 2.20
 - 20 AWG MAX INSULATION OD: 1.90
 - 22 AWG MAX INSULATION OD: 1.70
 - 24 AWG MAX INSULATION OD: 1.45

5. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

⑥ WIRE SIZE MARKING IN APPROXIMATE LOCATON SHOWN.

⑦ COLOR CODE MARKING, STRAIGHT LINE.

⑧ ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C DAILY 11 JUN 2009		Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
CHK O.SAGIE 11 JUN 2009		APVD - NAME		ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, CLOSED END	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.5 1 PLC ±0.13 2 PLC ±.13 3 PLC ±.13 4 PLC ±.13 ANGLES ±.13		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266	
MATERIAL 		FINISH 		SIZE A2	
WEIGHT -		CAGE CODE 00779		DRAWING NO C-2106489	
CUSTOMER DRAWING		RESTRICTED TO -		SCALE 6.1	
				SHEET 1 OF 3	
				REV A	

LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

D

D

C





C

B

B

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C DAILY 11JUN2009	Tyco Electronics Harrisburg, PA 17105-3608			
		CHK O OSAGIE 11JUN2009	NAME			
		APVD -	ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, CLOSED END			
DIMENSIONS: mm		PRODUCT SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	A2	00779	C-2106489	-
MATERIAL		WEIGHT -	SCALE 6:1 SHEET 2 OF 3 REV A			
		CUSTOMER DRAWING				



LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

D


C

B

A



SECTION Y-Y



D

C

B

A

2106489-2 SHOWN IN POCKET TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C DAILY 11JUN2009	Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS:		CHK O OSAGIE 11JUN2009	NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, CLOSED END			
mm		APVD -				
		PRODUCT SPEC	SIZE A200779C-2106489			
		APPLICATION SPEC				
		WEIGHT	SCALE 6:1			
		MATERIAL				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING	SHEET 3 OF 3			
0 PLC ±			REV A			
1 PLC ±0.5						
2 PLC ±0.13						
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						