

XVB7CM9

Light Module, Harmony XVB7 Modular Tower Light, Multi Pattern & Colored, Ø70mm, Clear Lens

Local Stock Code: On Stock



Main

Range of product	Harmony XVB7
Product or component type	Light module
Device composition	Standard lens
Device short name	XVB7
Mounting diameter	70 Mm
Signalling type	Multi function
Light source	LED, multi-colour
Material	PC (polycarbonate)
Net weight	0.107 Kg
Mounting position	Upright/Inverted

Complementary

Control type	DIP switch for color/light pattern
Service life in hours	50000 H
[Ue] rated operational voltage	24 V AC/DC
Rated operational voltage limits	21.6...26.4 V AC/DC
Current consumption	50 mA at 24 V AC 55 mA at 24 V DC
Inrush current	0.5 A
Electrical shock protection class	Class II
[Ui] rated insulation voltage	50 V
[Uimp] rated impulse withstand voltage	0.5 KV

Environment

Pollution degree	2
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP66
NEMA degree of protection	Type 4/4X/12/13 indoor use only
Vibration resistance	6 gn, amplitude = +/- 0.5 mm (f = 10...500 Hz)in operation

Shock resistance	30 gn (duration = 6 ms) for in operation
Standards	UL 60947-5-1 IEC 60947-5-1 CSA C22.2 No 60947-5-1
Product certifications	cULus[RETURN]CCC[RETURN]RCM[RETURN]UKCA[RETURN]CE

Ordering and shipping details

Category	US10CS222612
Discount Schedule	0CS2
GTIN	3606487129349
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 Cm
Package 1 Width	7.300 Cm
Package 1 Length	7.500 Cm
Package 1 Weight	107.000 G
Unit Type of Package 2	S03
Number of Units in Package 2	60
Package 2 Height	30 Cm
Package 2 Width	30 Cm
Package 2 Length	40 Cm
Package 2 Weight	6.912 Kg

Offer Sustainability

Recyclability potential, in %	89
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Total lifecycle Carbon footprint	17 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1.1357501415333293
Carbon footprint of the manufacturing phase [A1 to A3]	1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.03778626756415652
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.0005791771561749369
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	15.284640418658784
Carbon footprint of the use phase [B2, B3, B4, B6]	15 kg CO2 eq.
Mercury free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	0.10357696641852975
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Total lifecycle Carbon footprint	17
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
REACH Regulation	Reference contains Substances of Very High Concern above the threshold ↗
EU RoHS Directive	Compliant By Exemption ↗
End of life manual availability	End Of Life Information

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and n

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**