




AMP CT

TE Internal #: 175778-3  
Housing, Receptacle, Wire-to-Board, 3 Position, 2 mm [.078 in]  
Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable,  
Power & Signal

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >  
AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Housing**  
Connector & Housing Type: **Receptacle**  
Connector System: **Wire-to-Board**  
Number of Positions: **3**  
Centerline (Pitch): **2 mm [.078 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

|                                   |               |
|-----------------------------------|---------------|
| Connector Product Type            | Housing       |
| Connector & Housing Type          | Receptacle    |
| Connector System                  | Wire-to-Board |
| Sealable                          | No            |
| Connector & Contact Terminates To | Wire & Cable  |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 3 |
| Number of Rows      | 1 |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 125 VAC |
|-------------------|---------|

Contact Features

|  |  |
|--|--|
|  |  |
|--|--|



|                |        |
|----------------|--------|
| Contact Layout | Inline |
|----------------|--------|

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

|                         |                            |
|-------------------------|----------------------------|
| Mating Retention        | With                       |
| Connector Mounting Type | Cable Mount (Free-Hanging) |

Housing Features

|                    |               |
|--------------------|---------------|
| Housing Material   | 66Nylon       |
| Centerline (Pitch) | 2 mm[.078 in] |
| Housing Color      | Natural       |

Dimensions

|                  |               |
|------------------|---------------|
| Connector Length | 8 mm[.315 in] |
| Connector Height | 4 mm[.157 in] |
| Connector Width  | 5.1 mm[.2 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -30 – 105 °C[-22 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

|                        |            |
|------------------------|------------|
| Approved Standards     | UL         |
| UL Flammability Rating | UL 94V-0   |
| UL File Number         | E28476     |
| UL Rating              | Recognized |
| Agency/Standard        | UL         |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                             |
|-----------------------------------------------|---------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                   |
| EU ELV Directive 2000/53/EC                   | Compliant                                   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold     |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2022 (223) |



Candidate List Declared Against: JAN 2022 (223)  
Does not contain REACH SVHC

|                           |                                                                                     |
|---------------------------|-------------------------------------------------------------------------------------|
| Halogen Content           | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability                                        |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 292203-1  
CT CARD EDGE CONN ASSY 6P

Also in the Series | AMP CT

PCB Connector Mounting(46)

PCB Headers & Receptacles(756)

Wire-to-Board Connector Assemblies & Housings(257)

Wire-to-Board Connector Contacts(8)

Customers Also Bought



TE Part #353908-5  
CT REC HSG 5P CRIMP TYPE WHITE

TE Part #179609-1  
AMP CT CRIMP TTYPE-2 REC CONT.

TE Part #2134078-1  
SHILED FINGER 1210 EMBOSS  
PACKING

TE Part #176282-6  
AMP UNIVERSAL POWER CAP 2P

TE Part #2155917-2  
PIPE, OUTSIDE

TE Part #2155922-1  
STUFFER, WIRE MCT

TE Part #2155923-1  
STUFFER, WIRE CT

TE Part #2155925-1  
BLADE, WIRE CUT MCT

Documents

Product Drawings

CT.CRIMP REC HSG 3P

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_175778-3\_D1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_175778-3\_D1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_175778-3\_D1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping AMP 2.0mm Pitch CT Receptacle Contact

English

Product Environmental Compliance

TE Material Declaration

English

175778-3

Housing, Receptacle, Wire-to-Board, 3 Position, 2 mm [.078 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable, Power & Signal



[Agency Approvals](#)

[CSA Certificate](#)

English