

Speed starter - CSS 1.5-1/3 - 1201511

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 1.5 kW, configurable motor protection, STO function up to SIL 3 / PL e, Push-in connection, single-phase load input



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4063151265700

Technical data

Dimensions

Width	45 mm
Height	210 mm
Depth	190 mm
Length	≤ 50 m (EMC compliance category C2)
	≤ 50 m (EMC compliance category C3)
	≤ 50 m (no EMC compliance)

Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C (without current derating)
	-20 °C ... 60 °C (with linear current derating)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Maximum altitude	≤ 2000 m
	> 2000 m (with derating)
Permissible humidity (operation)	90 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)
Degree of protection	IP20
	NEMA 1
Vibration (operation)	0,075 mm / 1g

Speed starter - CSS 1.5-1/3 - 1201511

Technical data

Ambient conditions

Shock (operation)	15g, 11 ms
-------------------	------------

Input

Designation	Mains
Number of phases	1
Input voltage	230 V AC 240 V AC
Input voltage range	110 V AC ... 240 V AC -15 % ... +10 %
Frequency range	47 Hz ... 63 Hz
Nominal current	15.8 A (no line reactor) 14.5 A (with line reactor)

Output

Nominal motor power	1.5 kW
Apparent power	3 kVA
Nominal output current (I _N)	7.5 A (4 kHz) 6.2 A (8 kHz) 4.1 A (16 kHz)
Output frequency	0 Hz ... 500 Hz
Power dissipation	67 W (2 kHz) 74 W (4 kHz) 70 W (8 kHz) 66 W (16 kHz) 9 W (stand by)
Output current	≤ 11.25 A (180 s) ≤ 5.625 A (180 s, during recovery time) ≤ 13.5 A (15 s) ≤ 3.75 A (15 s, during recovery time)
Recovery time	150 s (180 s) 12 s (15 s)
Overload time	30 s (180 s) 3 s (15 s)
Discharge time	3 min. (Intermediate circuit capacitors)

General

Cooling	Fan
EMC filter present	No
Number of phases	1

Standards and Regulations

Standards/regulations	IEC 61800-5-1 IEC 61800-3
Pollution degree	2

Speed starter - CSS 1.5-1/3 - 1201511

Technical data

Standards and Regulations

Vibration (operation)	0,075 mm / 1g
Shock (operation)	15g, 11 ms

Conformance/approvals

Designation	Safety Integrity Level (SIL, IEC 61800-5-2)
Identification	3
Designation	Performance Level (EN ISO 13849)
Identification	e

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 11.0	27142320
eCl@ss 9.0	27142320

ETIM

ETIM 7.0	EC000256
----------	----------

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 322526
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 322526
------------	--	---	---------------

Speed starter - CSS 1.5-1/3 - 1201511

Approvals

cULus Listed



Accessories

Accessories

Assembly adapter

Power distribution board - EM-CPS-225 - 1002634



Modular power distribution board with CrossLink[®] interface, 125 A, 3-pos., touch-proof and protection against polarity reversal, width: 225 mm

Power distribution board - EM-CPS-405 - 1002635



Modular power distribution board with CrossLink[®] interface, 125 A, 3-pos., touch-proof and protection against polarity reversal, width: 405 mm

Connection module - EM-CPS-TB3/63A - 1002633



Connection module with integrated spring-loaded terminals for cables from 1.5 to 16 mm², 3-pos., maximum 63 A

Connection module - EM-CPS-TB3/125A - 1070299



Connection module with box terminals for conductors from 6 to 50 mm², 3-pos., maximum 125 A

Fan

Speed starter - CSS 1.5-1/3 - 1201511

Accessories

Fan - EM-CSS-FAN-45 - 1276912



Replaceable fan for 45 mm wide CONTACTRON Speed Starters

Shroud

Shield connection - EM-CSS-MOTORSHIELD-45 - 1276916



Shroud for motor lines for 45 mm wide CONTACTRON Speed Starters

Shield connection - EM-CSS-CONTROLSHIELD-45 - 1276909



Shroud for control lines for 45 mm wide CONTACTRON Speed Starters

Phoenix Contact 2022 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>